



Retroreflective sensor OBR2000-R3-E1-P-L



- Ultra-small housing design
- DuraBeam Laser Sensors durable and employable like an LED
- 45° cable outlet for maximum mounting freedom under extremely tight space constraints


Laser retroreflective sensor, ultra-small design with M3 mounting, polarization filter, 2000 mm detection range, light on, NPN output, 2 m fixed cable



Function

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a

Dimensions



Technical Data

General specifications	
Effective detection range	0 2 m
Reflector distance	40 2000 mm
Threshold detection range	2.3 m
Reference target	H40 reflector


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Technical Data Light source laser diode modulated visible red light, 680 nm Light type Polarization filter Laser nominal ratings Note LASER LIGHT, DO NOT STARE INTO BEAM Laser class Wave length 680 nm Beam divergence > 5 mrad Pulse length approx. 3 µs Repetition rate approx. 16.6 kHz max. pulse energy Diameter of the light spot approx. 35 mm at a distance of 2000 mm Opening angle approx. 0.5 ° Optical face frontal Ambient light limit EN 60947-5-2: 30000 Lux Functional safety related parameters 800 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0% Indicators/operating means Operation indicator LED green, statically lit Power on, short-circuit: LED green flashing (approx. 4 Hz) Function indicator LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted **Electrical specifications** U_{B} 12 ... 24 V Operating voltage < 10 mA No-load supply current l_o Protection class Ш Output Switching type NC contact / light-on Signal output 1 NPN output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC Switching current max. 50 mA, resistive load Voltage drop U_{d} ≤ 1.5 V DC Switching frequency approx. 2 kHz Response time 250 µs Conformity EN 60947-5-2 Product standard EN 60825-1:2007 Laser safety Approvals and certificates **UL** approval E87056, cULus Recognized, Class 2 Power Source CCC approval CCC approval / marking not required for products rated ≤36 V IEC 60825-1 Complies with 21 CFR 1040.10 and 1040.11 except for deviations FDA approval pursuant to Laser Notice No. 50, dated June 24, 2007 **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) -30 ... 70 °C (-22 ... 158 °F) Storage temperature Mechanical specifications Housing width 7.5 mm Housing height 26 mm 13.8 mm Housing depth Degree of protection IP67 2 m fixed cable Connection Material PC/ABS and TPU Housing


Technical Data

Optical face	PMMA
Cable	PUR
Mass	approx. 20 g
Cable length	2 m

Connection




Assembly



1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver	

Characteristic Curve



Safety Information



CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people!

Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

The warning accompanies the device and should be attached in immediate proximity to the device.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation

exposure.

Accessories

1188	MH-R3-01	Mounting aid for sensors from the R3 series, mounting bracket
000011	MH-R3-02	Mounting aid for sensors from the R3 series, mounting bracket
11888	MH-R3-03	Mounting aid for sensors from the R3 series, mounting bracket
	MH-R3-04	Mounting aid for sensors from the R3 series, mounting bracket
	REF-H40	Reflector, rectangular 47.5 mm x 23.5 mm, mounting holes, fixing strap
	REF-H23	Reflector with mounting holes
	REF-MH20	Reflector with Micro-structure, rectangular 32 mm x 20 mm, mounting holes
	REF-MH23	Reflector with Micro-structure, rectangular 23 mm x 13.8 mm, diagonal mounting hole

