

Triangulation sensor (BGS) OBT30-R3-E0-P-L



- Ultra-small housing design
- DuraBeam Laser Sensors durable and employable like an LED
- 45° cable outlet for maximum mounting freedom under extremely tight space constraints
- Precision object detection, almost irrespective of the color


Laser triangulation sensor with background suppression, ultra-small design with M3 mounting, 30 mm sensing range, light on, NPN output, 2 m fixed cable




Function

The R3 series nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Dimensions





Technical Data

General specifications

Detection range
Reference target
Light source
Light type

7 ... 30 mm standard white, 100 mm x 100 mm laser diode modulated visible red light , 680 nm

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Black-white difference (6 %/90 %) Diameter of the light spot

Functional safety related parameters

Technical Data

Laser nominal ratings

Note Laser class Wave length Beam divergence Pulse length Repetition rate max. pulse energy

Opening angle Optical face Ambient light limit

Mission Time (T_M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator Function indicator Electrical specifications Operating voltage

MTTF_d

	LASER LIGHT , DO NOT STARE INTO BEAM
	1
	680 nm
	> 5 mrad
	approx. 3 µs
	approx. 16.6 kHz
	9.5 nJ
	< 5 % at 30 mm
	< 1 mm at a distance of 30 mm
	approx. 2 °
	frontal
	EN 60947-5-2 : 30000 Lux
	000 -
	800 a
	20 a
	0 %
	LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz)
	LED yellow: lights when object is detected
U _B	12 24 V
I ₀	< 10 mA
-0	
	NO contact / light-on
	1 NPN output, short-circuit protected, reverse polarity protected, open collector
	max 30 V DC


OBT30-R3-E0-P-L

1 5 5	5	
No-load supply current	I ₀	< 10 mA
Protection class		III
Output		
Switching type		NO contact / light-on
Signal output		1 NPN output, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 50 mA , resistive load
Voltage drop	U_d	≤ 1.5 V DC
Switching frequency	f	approx. 2 kHz
Response time		250 μs
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
CCC approval		CCC approval / marking not required for products rated \leq 36 V
FDA approval		IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-30 70 °C (-22 158 °F)
Mechanical specifications		
Housing width		7.5 mm
Housing height		26 mm
Housing depth		13.8 mm
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		PC/ABS and TPU
Optical face		PC
Cable		PUR
Mass		approx. 20 g
Cable length		2 m


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

Connection Assignment




Assembly



_			
ŀ	1	Operating display	green
2	2	Signal display	yellow
3	3	Emitter	
4	4	Receiver	

Characteristic Curve

Light spot diameter Diameter in mm 1.0 0.5 0 -0.5 -1.0 -1.5 10 15 35 40 Distance in mm 0 20 25 30 5 -{·--• • • • • • • • **Detection ranges** Object colour



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

3

Safety Information



Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people! Maintenance and repairs should only be carried out by authorized service personnel! Attach the device so that the warning is clearly visible and readable. The warning accompanies the device and should be attached in immediate proximity to the device. Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories

,	MH-R3-01	Mounting aid for sensors from the R3 series, mounting bracket
, ;;; III	MH-R3-02	Mounting aid for sensors from the R3 series, mounting bracket
· • • • • • • • • • • • • • • • • • • •	MH-R3-03	Mounting aid for sensors from the R3 series, mounting bracket
00011	MH-R3-04	Mounting aid for sensors from the R3 series, mounting bracket

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

4