


Triangulation sensor with background suppression for standard applications, miniature design, 50 mm detection range, red light, light on, NPN output, 200 mm fixed cable with plug M8, 4-pin

Function

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options.

Dimensions



Technical Data

General specifications		
Detection range	3 50 mm	
Reference target	standard white, 100 mm x 100 mm	
Light source	LED	
Light type	modulated visible red light , 630 nm	

Pepperl+Fuchs Group

www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



1


Technical Data

Black-white difference (6 %/90 %) < 15 % at 50 mm Angle deviation approx. 2 ° Diameter of the light spot approx. 3.5 mm at a distance of 50 mm Opening angle approx. 2 ° Optical face frontal Ambient light limit EN 60947-5-2 : 30000 Lux Functional safety related parameters 800 a	
Diameter of the light spotapprox. 3.5 mm at a distance of 50 mmOpening angleapprox. 2 °Optical facefrontalAmbient light limitEN 60947-5-2 : 30000 LuxFunctional safety related parameters	
Opening angle approx. 2 ° Optical face frontal Ambient light limit EN 60947-5-2 : 30000 Lux	
Optical face frontal Ambient light limit EN 60947-5-2 : 30000 Lux Functional safety related parameters EN 60947-5-2 : 30000 Lux	
Ambient light limit EN 60947-5-2: 30000 Lux Functional safety related parameters EN 60947-5-2: 30000 Lux	
Functional safety related parameters	
MTTE ₄ 800 a	
u	
Mission Time (T _M) 20 a	
Diagnostic Coverage (DC) 0 %	
Indicators/operating means	
Operation indicator LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 H	lz)
Function indicator LED yellow ON: lights when object is detected	
Electrical specifications	
Operating voltage U _B 10 30 V DC , class 2	
No-load supply current I ₀ < 10 mA	
Protection class III	
Output	
Switching type NO contact / light on	
Signal output 1 NPN output, short-circuit protected, reverse polarity protected, open collector	
Switching voltage max. 30 V DC	
Switching current max. 50 mA , resistive load	
Voltage drop $U_d \leq 1.5 V DC$	
Switching frequency f approx. 800 Hz	
Response time 600 µs	
Conformity	
Product standard EN 60947-5-2	
Approvals and certificates	
UL approval E87056, cULus Recognized, Class 2 Power Source	
CCC approval / marking not required for products rated ≤36 V	
Ambient conditions	
Ambient temperature -25 60 °C (-13 140 °F)	
Storage temperature -30 70 °C (-22 158 °F)	
Mechanical specifications	
Housing width 7.5 mm	
Housing height 24 mm	
Housing depth 11.2 mm	
Degree of protection IP67	
Connection 200 mm fixed cable with 4-pin, M8x1 connector	
Material	
Housing PC/ABS and TPU	
Optical face PC	
Cable PUR	
Installation Fixing screws , 2 x M2 allen head screws included with delivery	
Mass approx. 20 g	
Cable length 200 mm	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

2

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Assembly




1	Operating display	green
2	2 Signal display yello	
3	Emitter	
4	Receiver	


Characteristic Curve



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Characteristic Curve



Accessories

	MH-R2-01	Mounting aid for R2 series, Mounting bracket
())	MH-R2-02	Mounting aid for R2 series, Mounting bracket
	MH-R2-03	Mounting aid for R2 series, Mounting bracket
	MH-R2-04	Mounting aid for R2 series, Mounting bracket
6/	V31-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey
ø /	V31-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

4