

Triangulation sensor (BGS) OBT50-R2-E2-0,2M-V31-P-L



- Ultra-small housing design
- DuraBeam Laser Sensors durable and employable like an LED
- 45° cable outlet for maximum mounting freedom under extremely tight space constraints
- Precision object detection, almost irrespective of the color


Laser triangulation sensor with background suppression, ultra-small design with M2 mounting, 50 mm sensing range, light on, PNP output, 200 mm fixed cable with plug M8, 4-pin



Function

The R2 series nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Dimensions




Technical Data

| General specifications | |
|------------------------|--------------------------------------|
| Detection range | 7 50 mm |
| Reference target | standard white, 100 mm x 100 mm |
| Light source | laser diode |
| Light type | modulated visible red light , 680 nm |



Technical Data

Laser nominal ratings Note LASER LIGHT, DO NOT STARE INTO BEAM Laser class 680 nm Wave length Beam divergence > 5 mrad Pulse length approx. 3 µs Repetition rate approx. 16.6 kHz 9.5 nJ max. pulse energy Black-white difference (6 %/90 %) < 10 % at 50 mm Diameter of the light spot approx. 0.8 mm at a distance of 50 mm Opening angle approx. 2 Optical face frontal EN 60947-5-2: 30000 Lux Ambient light limit Functional safety related parameters MTTF_d 800 a 20 a Mission Time (T_M) 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow ON: lights when object is detected **Electrical specifications** Operating voltage U_{B} 12 ... 24 V No-load supply current < 10 mAProtection class Ш Output Switching type NO contact / light-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector max. 30 V DC Switching voltage Switching current max. 50 mA, resistive load Voltage drop U_{d} ≤ 1.5 V DC Switching frequency approx. 2 kHz Response time 250 μs Conformity Product standard EN 60947-5-2 Standard conformity Standards EN 60947-5-2:2007 EN 60947-5-2/A1:2012 EN 60825-1:2007 UL 60947-5-2: 2014 Approvals and certificates **UL** approval E87056, cULus Recognized, Class 2 Power Source CCC approval CCC approval / marking not required for products rated ≤36 V IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations FDA approval pursuant to Laser Notice No. 50, dated June 24, 2007 **Ambient conditions** -20 ... 60 °C (-4 ... 140 °F) Ambient temperature -30 ... 70 °C (-22 ... 158 °F) Storage temperature Mechanical specifications 7.5 mm Housing width



Housing height

Housing depth Degree of protection

Optical face

Connection

Material Housing 24 mm 11.2 mm

IP67

PC


PC/ABS and TPU

200 mm fixed cable with 4-pin, M8x1 connector

Technical Data

| Cable | PUR |
|--------------|--|
| Installation | Fixing screws, 2 x M2 allen head screws included with delivery |
| Mass | approx. 10 g |
| Cable length | 200 mm |

Connection




Connection Assignment




Wire colors in accordance with EN 60947-5-2


| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue) |
| 4 | BK | (black) |

Assembly



| 1 | Operating display | green |
|---|-------------------|--------|
| 2 | Signal display | yellow |
| 3 | Emitter | |
| 4 | Receiver | |





Safety Information



CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Laser Class 1 Information
The irradiation can lead to irritation especially in a dark environment. Do not point at people!
Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

The warning accompanies the device and should be attached in immediate proximity to the device.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

| Acc | | \sim | | - |
|-----|------|--------|---------|-----|
| | J-1~ | 1-4- | 1 - 1 - | ٠.٠ |

| | · | |
|------|---------------|--|
| 6/ | V31-WM-2M-PUR | Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey |
| W. | MH-R2-01 | Mounting aid for R2 series, Mounting bracket |
| 1370 | MH-R2-02 | Mounting aid for R2 series, Mounting bracket |
| | MH-R2-03 | Mounting aid for R2 series, Mounting bracket |
| | MH-R2-04 | Mounting aid for R2 series, Mounting bracket |