


Laser triangulation sensor with background suppression, ultra-small design with M3 mounting, 50 mm sensing range, light on, PNP output, 200 mm fixed cable with plug M8, 3-pin



Function

The R3 series nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Dimensions



Technical Data

General specifications		
Detection range	7 50 mm	
Reference target	standard white, 100 mm x 100 mm	
Light source	laser diode	
Light type	modulated visible red light , 680 nm	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Laser nominal ratings Note LASER LIGHT, DO NOT STARE INTO BEAM Laser class 1 Wave length 680 nm Beam divergence > 5 mrad Pulse length approx. 3 µs Repetition rate approx. 16.6 kHz max. pulse energy 9.5 nJ Black-white difference (6 %/90 %) < 10 % at 50 mm Diameter of the light spot approx. 0.8 mm at a distance of 50 mm Opening angle approx. 2 ° Optical face frontal Ambient light limit EN 60947-5-2 : 30000 Lux TTFd 800 a Mission Time (Tw) 20 a Diagnostic Coverage (DC) 0%
Laser class1Wave length680 nmBeam divergence> 5 mradPulse lengthapprox. 3 μsRepetition rateapprox. 16.6 kHzmax. pulse energy95 nJBlack-white difference (6 %/90 %)< 10 % at 50 mm
Beam divergence > 5 mrad Pulse length approx. 3 μs Repetition rate approx. 16.6 kHz max. pulse energy 9.5 nJ Black-white difference (6 %/90 %) < 10 % at 50 mm
Beam divergence > 5 mrad Pulse length approx. 3 μs Repetition rate approx. 16.6 kHz max. pulse energy 9.5 nJ Black-white difference (6 %/90 %) < 10 % at 50 mm
Pulse lengthapprox. 3 µsRepetition rateapprox. 16.6 kHzmax. pulse energy9.5 nJBlack-white difference (6 %/90 %)<10 % at 50 mm
Repetition rateapprox. 16.6 kHzmax. pulse energy9.5 nJBlack-white difference (6 %/90 %)<10 % at 50 mm
max. pulse energy9.5 nJBlack-white difference (6 %/90 %)<10 % at 50 mm
Black-white difference (6 %/90 %) < 10 % at 50 mm
Diameter of the light spotapprox. 0.8 mm at a distance of 50 mmOpening angleapprox. 2 °Optical facefrontalAmbient light limitEN 60947-5-2 : 30000 LuxFunctional safety related parametersMTTFd800 aMission Time (T_M)20 aDiagnostic Coverage (DC)0%
Opening angleapprox. 2 °Optical facefrontalAmbient light limitEN 60947-5-2 : 30000 LuxFunctional safety related parametersMTTFd800 aMission Time (T_M)20 aDiagnostic Coverage (DC)0%
Optical facefrontalAmbient light limitEN 60947-5-2 : 30000 LuxFunctional safety related parametersMTTFd800 aMission Time (T_M)20 aDiagnostic Coverage (DC)0%
Ambient light limit EN 60947-5-2 : 30000 Lux Functional safety related parameters MTTFd MTTFd 800 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0%
Functional safety related parameters MTTF _d 800 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0%
MTTFd800 aMission Time (T_M)20 aDiagnostic Coverage (DC)0 %
Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 %
Diagnostic Coverage (DC) 0 %
Operation indicator LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz
Function indicator LED yellow: lights when object is detected
Electrical specifications
Operating voltage U _B 12 24 V
No-load supply current $I_0 < 10 \text{ mA}$
Protection class III
Output
Switching type NO contact / light-on
Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector
Switching voltage max. 30 V DC
Switching current max. 50 mA, resistive load
Voltage drop $U_d \leq 1.5 \text{ V DC}$
Switching frequency f approx. 2 kHz
Response time 250 µs
Conformity
Product standard EN 60947-5-2
Standard conformity
Standards EN 60947-5-2:2007 EN 60947-5-2/A1:2012 EN 60825-1:2007 UL 60947-5-2: 201
Approvals and certificates
UL approval E87056, cULus Recognized, Class 2 Power Source
CCC approval CCC approval / marking not required for products rated ≤36 V
FDA approval IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviation pursuant to Laser Notice No. 50, dated June 24, 2007
Ambient conditions
Ambient temperature -20 60 °C (-4 140 °F)
Storage temperature -30 70 °C (-22 158 °F)
Mechanical specifications
Housing width 7.5 mm
Housing height 26 mm
Housing depth 13.8 mm
Degree of protection IP67
Connection 200 mm fixed cable with 3-pin, M8 x 1 connector
Material
Housing PC/ABS and TPU
Optical face PC

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Release date: 2023-09-06 Date of issue: 2023-09-06 Filename: 70141914_eng.pdf



Technical Data

Cable	PUR
Mass	approx. 10 g
Cable length	200 mm

Connection Assignment




Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
3	BU	(blue)
4	BK	(black)

Assembly




1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3

Characteristic Curve



Safety Information



CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Release date: 2023-09-06 Date of issue: 2023-09-06 Filename: 70141914_eng.pdf

4

Safety Information

Laser Class 1 Information The irradiation can lead to irritation especially in a dark environment. Do not point at people! Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable. The warning accompanies the device and should be attached in immediate proximity to the device. Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories

٢/	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey
1, 000 M	MH-R3-01	Mounting aid for sensors from the R3 series, mounting bracket
(1) (2) (2) (2) (1) (2) (1) (2) (1) (2) (2) (2) (2) (2) (2) (2) (2) (2) (2	MH-R3-02	Mounting aid for sensors from the R3 series, mounting bracket
0000 HT	MH-R3-03	Mounting aid for sensors from the R3 series, mounting bracket
° ° ° 11	MH-R3-04	Mounting aid for sensors from the R3 series, mounting bracket

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

5