

Thru-beam sensor (pair) OBE10M-R3-SP1-0,2M-V3-P-L



- Ultra-small housing design
- DuraBeam Laser Sensors durable and employable like an LED
- 45° cable outlet for maximum mounting freedom under extremely tight space constraints


Laser thru-beam sensor, ultra-small design with M3 mounting, 10 m detection range, push-pull output, 200 mm fixed cable with plug M8, 3-pin



Function

The R3 series nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Dimensions



Technical Data

System components			
Emitter	OBE10M-R3-S-0,2M-V3-P-L		
Receiver	OBE10M-R3-P1-0,2M-V3-P-L		
General specifications			
Effective detection range	0 10 m		


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 70141994_eng.pdf

Technical Data Threshold detection range 15 m Light source laser diode Light type modulated visible red light, 680 nm Laser nominal ratings Note LASER LIGHT, DO NOT STARE INTO BEAM Laser class Wave length 680 nm Beam divergence > 5 mrad Pulse length approx. 3 µs Repetition rate approx. 16.6 kHz max. pulse energy Diameter of the light spot approx. 20 mm at a distance of 10 m Opening angle approx. 0.5 ° Optical face frontal Ambient light limit EN 60947-5-2: 30000 Lux Functional safety related parameters 806 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0% Indicators/operating means Operation indicator LED green, statically lit Power on, short-circuit: LED green flashing (approx. 4 Hz) Function indicator Receiver: LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve; OFF when light beam is interrupted **Electrical specifications** U_B 12 ... 24 V Operating voltage No-load supply current I_0 Emitter: ≤ 10 mA Receiver: ≤ 8 mA Protection class Ш Input Test input Test of switching function at 0 V Output Switching type The default setting is: PNP normally-open/dark-on; NPN normally-closed/light-on Signal output Push-pull output, short-circuit protected, reverse polarity protected Switching voltage max. 30 V DC max. 50 mA, resistive load Switching current U_d ≤ 1.5 V DC Voltage drop Switching frequency approx. 2 kHz Response time 250 µs Conformity Product standard EN 60947-5-2 EN 60825-1:2007 Laser safety Approvals and certificates **UL** approval E87056, cULus Recognized, Class 2 Power Source CCC approval CCC approval / marking not required for products rated ≤36 V FDA approval IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007 Ambient conditions -20 ... 60 °C (-4 ... 140 °F) Ambient temperature -30 ... 70 °C (-22 ... 158 °F) Storage temperature **Mechanical specifications** 7.5 mm Housing width Housing height 26 mm Housing depth 13.8 mm IP67 Degree of protection

Technical Data Connection 200 mm fixed cable with 3-pin, M8 x 1 connector Material Housing PC/ABS and TPU Optical face PC Cable PUR Mass approx. 10 g per sensor Cable length 200 mm

Connection






Connection Assignment




Wire colors in accordance with EN 60947-5-2


BN	(prown)
BU	(blue)
BK	(black)
	BU

Assembly



2 Signal display yello	ı	
	N	
3 Emitter	Emitter	
4 Receiver		





Safety Information



CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

CLASS 1 ASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Laser Class 1 Information
The irradiation can lead to irritation especially in a dark environment. Do not point at people!
Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

The warning accompanies the device and should be attached in immediate proximity to the device.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories

61	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey
1188	MH-R3-01	Mounting aid for sensors from the R3 series, mounting bracket
:::11	MH-R3-02	Mounting aid for sensors from the R3 series, mounting bracket
00011	MH-R3-03	Mounting aid for sensors from the R3 series, mounting bracket
	MH-R3-04	Mounting aid for sensors from the R3 series, mounting bracket