

Retroreflective sensor with polarization filter, plastic housing, 3 m detection range, red light, light on, DC version, PNP output, no operating element, fixed cable with M8 plug




Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.



Dimensions



Technical Data

General specifications		
Effective detection range		0 2.7 m
Reflector distance		0.02 2.7 m (0.02 1 m on OFR-100/100 optical reflective film)
Threshold detection range		3 m
Reference target		H50 reflector
Light source		LED
Light type		modulated visible red light
Polarization filter		yes
Diameter of the light spot		approx. 200 mm at a distance of 3 m
Opening angle		approx. 4 °
Optical face		frontal
Ambient light limit		EN 60947-5-2
Functional safety related parameters		
MTTF _d		860 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green: power on
Function indicator		LED yellow: lights up when receiving the light beam ; flashes when falling short of the operating reserve; OFF when light beam is interrupted
Electrical specifications		
Operating voltage	UB	10 30 V DC

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Release date: 2023-06-15 Date of issue: 2023-06-15 Filename: 70142204_eng.pdf

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

ML100-54-F/25/103/115a/154

Technical Data		
Photo		
Ripple		max. 10 %
No-load supply current	lo	< 20 mA
Output		
Switching type		light-on
Signal output		1 PNP output, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA , resistive load
Voltage drop	U _d	≤ 1.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated \leq 36 V
Ambient conditions		
Ambient temperature		-30 60 °C (-22 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		20 mm
Degree of protection		IP67
Connection		300 mm fixed cable with 3-pin, M8 x 1 connector
Material		
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 20 g
Tightening torque, fastening screws		0.6 Nm
Cable length		0.3 m

Connection



Connection Assignment



 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr


 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Connection Assignment

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
3	BU	(blue)
4	BK	(black)

Indication



Mounting


Mounting

The sensors can be mounted directly via through-holes or by using a mounting bracket or a clamp component. Mounting brackets and clamp components are available as accessories. Ensure that the surface is flat to avoid housing distortion during mounting and fixing.

Secure nut and bolt with spring washers to prevent misalignment of the sensor.

Adjusting the Sensor: Apply the operating voltage to the sensor. The power indicator lights green. Mount a suitable reflector opposite the retroreflecitve sensor. Align the sensor (without object) roughly with the reflector. Then adjust the sensor to the reflector by tilting it horizontally and vertically until the yellow signal indicator is permanently lights up. If the alignment is inaccurate, the yellow signal indicator flashes.

Characteristic Curve



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Retroreflective sensor

Characteristic Curve

Relative received light strength (typical) Reflector type: H85-2 20 mm 4 m C110-2 20 mm 35 m H50 20 mm 3 m 20 mm OFR-100/100 1.2 m OFR 20 mm x 20 mm 20 mm 0.8 m Stability control Stability control > 1.5 100.0 H85-2 Stability control < 1.5 C110-2 -----H50 . -OFR-100/100 OFR 20 mm x 20 mm 10.0 _ 1.5 1.0 0. 0.5 30 40 0 1.0 1.5 20 25 35 4 5 5.0 Distance X [m]

System Description

System Description The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.

Commissioning

Commissioning Check Object Detection: Check as follows if the sensor detects objects as intended.

Position the object in the beam path of the sensor.

Once the object is detected, the yellow signal indicator goes out. As soon as the object leaves the beam path of the sensor, the yellow signal indicator permanently lights up again.


Maintenance

Maintenance

Cleaning: If reception deteriorates, e. g. due to dirt, the yellow signal indicator of the receiver flashes. Clean the optical interfaces of the sensor (e. g. lenses) at regular intervals. Servicing: Check the mounting screw connections and the electrical plug connections regularly.

Accessories				
Contraction of the second seco	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
*	OMH-F10-ML100	Mounting aid for ML100 series		
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket		
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket		
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Retroreflective sensor

Acces	Accessories		
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket	
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket	
	OMH-10	Mounting aid for ML100 series	
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole	
	REF-H60-2	Reflector with mounting holes	
	REF-H33	Reflector with screw fixing	
	OFR-70-2	Reflective tape 70 mm x 70 mm	
	OMH-ML100-08	Mounting aid for ML100 series, Snap-in	
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes	
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap	
	OFR-100/100	Reflective tape 100 mm x 100 mm	
61	V3-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 3-pin, PUR cable grey	
6/	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey	

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com