

Metal code bar

PGV000002M- CAMG30x500-000001-B


- High temperature resistance
- High mechanical stability
- Easily exchangeable
- Chemically highly resistant

DataMatrix metal code bars for positioning PGV read heads

Function

Rugged Data Matrix metal code bars made of anodized aluminum for use on the ground in camera-based track guidance. Depending on the application, the code bars can be glued directly to the floor, or glued into special carrier profile rails. The code bars are available in modular lengths of 100, 200, and 500 mm.

Dimensions



Technical Data

General specifications	
Total length	2 m
Start position	1 m
Code bar segment	
Length	500 mm
Width	30 mm
Ambient conditions	
Operating temperature	-40 ... 80 °C (-40 ... 176 °F)
Installation temperature	10 ... 40 °C (50 ... 104 °F)
Environmental resistance	UV radiation Humidity
Chemical resistance	Oils Grease Fuels Aliphatic solvents Weak acids
Mechanical specifications	
Material thickness	1 mm
Material	Aluminum
Mounting type	adhesive
Mass	83 g / m
Manufacturing tolerance	± 4 mm/m

Release date: 2022-05-04 Date of issue: 2022-05-04 Filename: 70144669-100018_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Mounting

Preparing the Base Surface

1. Use clean cleaning cloths (free from lint and plasticizers) to clean the surfaces.
2. Use cleaning agents appropriate for the level of surface contamination, for example n-Heptane, ethanol, or a 50:50 mixture of isopropanol and water.
3. Clean the surface until it is completely dry and free of dust, oil, oxides, release agents, and other contaminants.
4. Ensure that the surface is dry, clean, and stable.

Adhesive Strength

Metal	Material with high-energy surfaces	Material with low-energy surfaces
33 N/25 mm	32 N/25 mm	31 N/25 mm

Material thickness: 1 mm code bar + 0.13 mm adhesive

Processing Instructions

During bonding, the pressure should be as high as possible, and the temperature should be at least +10 °C. The higher the pressure and temperature, the better the adhesive will penetrate the pores of the base surface. This allows higher adhesive strength values to be achieved. It takes approx. 72 hours for the adhesive to cure.

Type Code

Structure of the type code

P	G	V	(1)	(1)	(1)	(1)	(1)	(1)	M	-	C	A	M	(2)	(3)	(3)	x	(4)	(4)	(4)	-	(5)	(5)	(5)	(5)	(5)	(5)	-	B
----------	----------	----------	-----	-----	-----	-----	-----	-----	----------	---	----------	----------	----------	-----	-----	-----	----------	-----	-----	-----	---	-----	-----	-----	-----	-----	-----	---	----------

PGV	Sensor Type
PGV	Position Guided Vision

(1) (1) (1) (1) (1) (1)	Total length of the code bar
1 ... 10,000	The total length of the code bar is determined by the number of individual code bar segments. The code bars can be ordered in 1 m units.

M	Unit
M	Length in meters

CAM	Code Bar
C	Code bar
A	Absolute code bar
M	Metal code bar

(2)	Mounting Type
G	Mounted by bonding with the adhesive applied to the back. Bonded directly on the floor or in special profile rails.
H	Mounted by screwing or riveting to the support material.

(3) (3)	Code Bar Width
30	Width of the code bar in mm for mounting by bonding.
50	Width of the code bar in mm for mounting by screwing or riveting.

(4) (4) (4)	Code Bar Length
100	Length of the individual code bars in mm.
200	Length of the individual code bars in mm.
500	Length of the individual code bars in mm.

(5) (5) (5) (5) (5) (5)	Start position
1 ... 9,999	Start position of the code bars in m.

B	Version Information
B	Version B

Release date: 2022-05-04 Date of issue: 2022-05-04 Filename: 70144669-100018_eng.pdf