


Drive-over profile rail for creating endless rail sections and for additionally attaching a control code on the left-hand side

Dimensions



Technical Data

General specifications	
Length	535.6 mm
Width	85 mm
Ambient conditions	
Operating temperature	-40 80 °C (-40 176 °F)
Installation temperature	10 40 °C (50 104 °F)
Mechanical specifications	
Material thickness	4 mm
Material	AlMg4.5Mn0.7

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com



Drive-over profile rail

PGV-PR-SM-CONTROL500L

Technical Data		
Surface	ELOX-E0EV1-15	

300 g

Mounting

Mass

Drive-over profile rails are screwed directly to the floor. Alternatively, the drive-over profile rails can be glued to the subfloor. The corresponding metal code bar is then inserted into the drive-over profile rails via the self-adhesive rear side. If necessary, metal code bars that have been glued in can be replaced by levering them out.

Accessories			
	PGV-PR-SM-CONT500	Drive-over rail to realize endless tracks	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

2