

Protection Module for Surge Protection Barrier

M-LB-4282.M


- Protection module for 2 signal lines
- Nominal voltage 230 V
- Protection module for non-grounded signal lines
- Max. surge current (8/20 µs) 6 kA
- Uninterruptable operation (auto reset)
- Status indication
- Mounting on base module, pluggable
- Up to SIL 3 acc. to IEC/EN 61508

CE SIL 3

Function

The protection module limits induced transients of different causes, e. g. lightning or switching operations. The limitation is achieved by diverting the current to earth and limiting the signal circuit voltage during the duration of the overvoltage pulse.
The device is a spare part for the corresponding 2-part surge protection barrier. The device is not to be used as a stand-alone device.
The device has a status indication at the front.
The device can be replaced without tools by locking levers.

Wiring Diagram



Zone 2

Technical Data


General specifications		
Device type		Type 2/P3 acc. to EN 61643-11
Number of protected signal lines		2
Topology		non-grounded
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 3
Electrical specifications		
Connection		via base module
Leakage current		< 50 nA bei U_c , line-line < 50 nA bei U_c , line-earth
Nominal voltage	U_N	230 V
Maximum continuous operating voltage	U_c	250 V AC and 320 V DC

Release date: 2026-08-21 Date of issue: 2026-08-21 Filename: 70155099_eng.pdf

Technical Data

Nominal load current	I_L	3 A at 80 °C (176 °F)
Series resistance		0 Ω per line
Impulse discharge current (10/350 µs)	I_{imp}	0.5 kA per line
Nominal discharge current (8/20 µs)	I_n	3 kA per line
Total discharge current (8/20 µs)	I_{total}	6 kA
Voltage protection level	U_p	max. 1100 V line-earth for nominal discharge current I_n
Impulse reset time		< 30 ms
Cut-off frequency	f_G	200 MHz , line-line
Indicators/settings		
Display elements		status display operating state (green) fault indication (red)
Conformity		
Degree of protection		IEC 60529:2013
Functional safety		IEC/EN 61508:2010
Surge protective devices for low voltage		EN 61643-21:2001+A1:2009+A2:2013 IEC 61643-21:2001+A1:2008+A2:2012
Ambient conditions		
Ambient temperature		-40 ... 80 °C (-40 ... 176 °F)
Storage temperature		-40 ... 80 °C (-40 ... 176 °F)
Relative humidity		max. 95 % , without condensation
Corrosion resistance		acc. to ISA-71.04, severity level G3
Mechanical specifications		
Degree of protection		IP20
Connection		via base module
Material		
Housing		Polyamide PA 6.6
Mass		approx. 14 g
Dimensions		6 x 45 x 54 mm (0.24 x 1.77 x 2.15 inch) (W x H x D)
Mounting		pluggable in base module for mounting on 35 mm DIN mounting rail
Data for application in connection with hazardous areas		
EU-type examination certificate		
Internal capacitance	C_i	
General information		
Supplementary information		Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

Assembly



1	Status indication

Release date: 2026-08-21 Date of issue: 2026-08-21 Filename: 70155099_eng.pdf