

# Solenoid Driver KFD2-RCI-1

- 1-channel signal conditioner
- 24 V DC supply (Power Rail)
- Output 20.4 mA at 13.5 V DC
- 19 V DC ... 30 V DC input
- Test pulse immunity
- Line fault detection (LFD)
- Up to SIL 3 acc. to IEC/EN 61508

# **C € SIL** 3

### **Function**

This signal conditioner provides galvanic isolation between field circuits and control circuits.

The device can be used in emergency shutdown applications with HART positioners.

Via the logic input the positioner is energized or de-energized (emergency shutdown). Independent of the status, a second input enables HART communication with the positioner. With this the asset management system can request for example diagnostic information or can initiate a partial stroke test.

The HART communication also works with de-energized positioner.

If the device is operated via Power Rail, additionally a collective error message is available.

## **Application**


The device supplies power to safety valve controller with HART functionality.

The device supplies power to safety valve controller with FART functionality.

The device is controlled by means of a logic circuit. Voltage signals in a range of 19 V DC to 30 V DC are accepted as 1-signal. The 0-signal must be within a range of 0 V DC to 5 V DC. The current consumption of the logic input is about 40 mA. At full load, 13.5 V at 20.4 mA is available for the hazardous area load. Line fault detection of the field circuit is indicated by a red LED. The fault signal switches on if the field voltage is > 16 V for lead breakage (LB) or < 1 V for short circuit (SC).

This device provides the HART pass-trough for maintenance and diagnostic of the solenoid valve. The HART communication is available both in ON condition and in OFF condition of the solenoid.

## Connection



## **Technical Data**

#### **General specifications**

Digital Output

Functional safety related parameters



#### Technical Data Safety Integrity Level (SIL) SIL 3 Supply Connection Power Rail or terminals 14+, 15-Ur 19 ... 30 V DC Rated voltage Rated current $I_r$ < 35 mAPower consumption < 0.8 W Input Connection side control side Connection terminals 10+, 11-Test pulse length max, 2 ms from DO card Input current 40 mA at 19 ... 30 V DC 1-signal: 19 ... 30 V DC 0-signal: 0 ... 5 V DC Signal level < 1.2 W Power consumption Operating mode loop powered Output Connection side field side/control side Connection terminals 1+, 3- (terminals 1+, 2 for test loop) Internal resistor $R_i$ approx. 275 Ω Current $I_e$ ≤ 20.4 mA $U_{\rm e}$ ≥ 13.5 V Voltage Open loop voltage Us > 16 V Voltage 1-signal: > 13.5 V 1-signal: 20.4 A 0-signal: 4.2 mA Current Load max. 650 Ω Response time < 40 ms input to output Line fault detection short circuit voltage < 1 V, open circuit voltage > 16 V Output II Connection terminal 7: source (-) or sink (+), terminal 8: source (+), terminal 9: sink (-) Current 11 mA (source or sink mode) Voltage 9 ... 30 V sink mode from external supply Load max. 650 $\Omega$ , source mode , for HART $\geq$ 230 $\Omega$ pass-through of HART signal between input II and output Communication Galvanic isolation Field circuit/control circuit basic insulation according to IEC 61010-1, rated insulation voltage 300 Veff Input/power supply functional insulation, rated insulation voltage 50 Veff Output II/power supply functional insulation, rated insulation voltage 50 Veff Indicators/settings LEDs Display elements Control elements DIP switch Configuration via DIP switches Labeling space for labeling at the front **Directive conformity** Electromagnetic compatibility Directive 2014/30/EU EN 61326-1:2013 (industrial locations) Conformity Electromagnetic compatibility NE 21:2012 Degree of protection IEC 60529:2001 **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) Mechanical specifications IP20 Degree of protection Connection screw terminals


KFD2-RCI-1

# Technical Data

Solenoid Driver

Mass	approx. 150 g
Dimensions	20 x 119 x 115 mm (0.8 x 4.7 x 4.5 inch) (W x H x D) , housing type B2
Mounting	on 35 mm DIN mounting rail acc. to EN 60715:2001
General information	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

## **Assembly**



# **Matching System Components**

KFD2-EB2	Power Feed Module
UPR-03	Universal Power Rail with end caps and cover, 3 conductors, length: 2 m
UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
K-DUCT-GY	Profile rail, wiring comb field side, gray
K-DUCT-GY-UPR-03	Profile rail with UPR-03-* insert, 3 conductors, wiring comb field side, gray

# **Accessories** KF-ST-5GN Terminal block for KF modules, 3-pin screw terminal, green KF-CP Red coding pins, packaging unit: 20 x 6