

## Inertial measurement unit

### IMUF99PL-SC3600-0KB16V1501

- Dynamic inclination measurement despite external acceleration
- Adjustable ranges for compensation of external accelerations, disturbances
- Adjustable thresholds for detection of measured value overruns
- Measurement of inclination, acceleration and rotation rate in 3 axis each
- CAN bus with CANopen

Inertial measurement unit for inclination, acceleration and rotation rate measurement in 3-axis each




### Function

The IMUF99 is optimized to provide stabilized inclination and acceleration data as well as rotation rate data. The horizontal inclination can be reliably determined using the 3 measuring axis. The dynamic angle accuracy can be individually configured by selecting a compensation range to counteract the influence of external accelerations.

Different output types are selectable for the angle definition (Euler angle, Euler vector, quaternions). In addition, accelerations and rotation rates are reliably measured in the 3 measuring axis. For further optimization of the measured value quality, filters can be set to suppress external vibrations.

### Dimensions



### Technical Data

#### General specifications

Type	Inertial measurement unit 3-axis
Measuring technology	MEMS
<b>Inclination measurement</b>	
Measurement range	0 ... 360 °
Static accuracy	± 0.15 ° at 25 °C for inclination range ±45 ° ± 0.2 ° at 25 °C for inclination range ±90 ° ± 0.3 ° at 25 °C for inclination range 360 °
Dynamic accuracy	< 0.5 ° absolute, absolut, bei 25 °C über 360 ° Neigungsbereich
Resolution	0.01 °

Release date: 2023-10-09 Date of issue: 2023-10-09 Filename: 70159687\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PEPPERL+FUCHS**

## Technical Data

Repeat accuracy		$\pm 0.1^\circ$
Temperature influence		$\pm 0.015^\circ / K$
<b>Acceleration measurement</b>		
Measurement range		$\pm 4 g$
Linearity		$\pm 0,5\%$ of the measured value, up to $\pm 1 g$ for $-40 \dots +85^\circ C$
Resolution		0.001 g
Frequency range		0 ... 30 Hz
<b>Rotation rate measurement</b>		
Measurement range		$\pm 250^\circ/s$
Accuracy		$\pm 0.2^\circ/s$ at $25^\circ C$ in the measuring range $\pm 45^\circ/s$ $\pm 0.5^\circ/s$ at $25^\circ C$ in the measuring range $\pm 120^\circ/s$ $\pm 1^\circ/s$ at $25^\circ C$ in the measuring range $\pm 250^\circ/s$
Resolution		0.01 $^\circ/s$
<b>Functional safety related parameters</b>		
MTTF <sub>d</sub>		628 a
Mission Time (T <sub>M</sub> )		10 a
Diagnostic Coverage (DC)		0 %
<b>Indicators/operating means</b>		
Operation indicator		LED, yellow
Status indicator		LED, green
Error indicator		LED, red
<b>Electrical specifications</b>		
Operating voltage	U <sub>B</sub>	5 ... 30 V DC
No-load supply current	I <sub>0</sub>	$\leq 80$ mA
Power consumption	P <sub>0</sub>	$\leq 0.6$ W
<b>Interface</b>		
Interface type		CANopen
Node ID		0 ... 126 , programmable
Transfer rate		125 ... 1000 kBit/s , programmable
Termination		external
Cycle time		10 ... 655350 ms , programmable
<b>Standard conformity</b>		
Climatic testing		EN IEC 60068-2-38 , cyclic 12h + 12h, 94% humidity EN 60068-2-14 , test Na, $-50 \dots +85^\circ C$ , 10 cycles
Salt spray test		IEC 60068-2-52 , cyclic
Emitted interference		EN IEC 61000-6-4:2019 , EN 55011:2016+A1:2017+A11:2020
Noise immunity		EN IEC 61000-6-2:2019 , ISO 7637-2:2011 , ISO 7637-3:2016 , ISO 16750-2:2012
Shock resistance		EN 60068-2-27, 100 g, 6 ms
Vibration resistance		EN 60068-2-6, 20 g, 10 ... 2000 Hz
<b>Approvals and certificates</b>		
UL approval		E87056 , cULus Listed, General Purpose, Class 2 Power Source, Type 1 enclosure , if UL marking is marked on the product. For use in NFPA 79 Applications only. adapters providing field wiring on request
E1 Type approval		10R-06
<b>Ambient conditions</b>		
Ambient temperature		$-40 \dots 85^\circ C$ ( $-40 \dots 185^\circ F$ )
Storage temperature		$-40 \dots 85^\circ C$ ( $-40 \dots 185^\circ F$ )
<b>Mechanical specifications</b>		
Connection type		5-pin, M12 x 1 connector 5-pin, M12 x 1 socket internal bridged
Housing material		PA
Housing length		65 mm
Housing width		45 mm
Housing height		37 mm
Degree of protection		IP68 / IP69

Release date: 2023-10-09 Date of issue: 2023-10-09 Filename: 70159687\_eng.pdf


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.comUSA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.comGermany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com
 PEPPERL+FUCHS



**Technical Data**

Mass	265 g
<b>Factory settings</b>	
Node ID	16
Transfer rate	250 kBit/s
Cycle time	10 ms
Compensation range	4

**Connection**




**Connection Assignment**



**Operation**

Spatially fixed coordinate system (extrinsic reference to the horizontal plane) for P+F angles INX or INY  
 Angle range 0 ° ... 360 °




Release date: 2023-10-09 Date of issue: 2023-10-09 Filename: 70159687\_eng.pdf


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

**Operation**


**Body fixed coordinate system (intrinsic or co-rotating) for P+F angle INZ**  
 Angle range 0 ° ... 360 °



**Spatially fixed coordinate system (extrinsic reference to the horizontal plane) for Euler angle ZXZ**  
 Angle range - 180 ° ... +180 °














**Body fixed coordinate system (intrinsic or co-rotating) for Euler angle zy'x''**  
 Angle range -180 ° ... +180 °



Release date: 2023-10-09 Date of issue: 2023-10-09 Filename: 70159687\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Accessories


	<b>V15S-TR-CAN/DN-120R</b>	Terminal resistor for DeviceNet, CANOpen
	<b>V15-G-VT0,5M-PUR-U/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable violet, shielded, UL approved, drag chain suitable, salt water resistant
	<b>V15-G-VT1M-PUR-U/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable violet, shielded, UL approved, drag chain suitable, salt water resistant
	<b>V15-G-VT10M-PUR-U/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable violet, shielded, UL approved, drag chain suitable, salt water resistant
	<b>V15-G-VT5M-PUR-U/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable violet, shielded, UL approved, drag chain suitable, salt water resistant
	<b>V15-G-VT6M-PUR-U/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable violet, shielded, UL approved, drag chain suitable, salt water resistant
	<b>V15-G-BK0,3M-PUR-O2/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable 4-core twisted pairs black, shielded, UL approved, drag chain suitable, outdoor
	<b>V15-G-BK1M-PUR-O2/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable 4-core twisted pairs black, shielded, UL approved, drag chain suitable, outdoor
	<b>V15-G-BK10M-PUR-O2/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable 4-core twisted pairs black, shielded, UL approved, drag chain suitable, outdoor
	<b>V15-G-BK3M-PUR-O2/CAN-V15-G</b>	DeviceNet/CANOpen bus cable M12 socket straight to M12 plug straight A-coded, 5-pin, PUR cable 4-core twisted pairs black, shielded, UL approved, drag chain suitable, outdoor
	<b>CAN/USB-Configuration-Kit</b>	CAN/USB configuration kit containing CAN/USB converter, power supply and adapter/connection cables

## Mounting

### Mounting of the sensor

Sensors from the -F99 series consist of a sensor module and accompanying cast aluminum housing. Select a flat surface with minimum dimensions of 70 mm x 50 mm to mount the sensor.

Mount the sensor as follows:



1. Loosen the central screw under the sensor connection.
  2. Slide back the clamping element until you are able to remove the sensor module from the housing.
  3. Remove the sensor module from the housing
  4. Position the housing at the required mounting location and secure using four countersunk screws. Make sure that the heads of the screws do not protrude.
  5. Place the sensor module in the housing.
  6. Slide the clamping element flush into the housing. Check that the sensor element is seated correctly.
  7. Finally tighten the central screw.
- The sensor is now mounted correctly.