

Industrial Event Camera

VOC12M-F356-B12-V1D-CR2S


- Web interface for easy access to image and video files and livestream
- Video ring buffer with a pre-run buffer for automatic recording of video up to 900 seconds before and after a situation that requires fault analysis or documentation
- Trigger video/image capture via UDP, REST API, or a digital hardware input
- Find situations of interest quickly due to timestamped events
- REST API for full HMI integration of all camera functions

Event camera for recording video sequences with Livestream function.

Function

The industrial event camera enables efficient remote diagnostics and automatic documentation through event-controlled video recordings. In the event of a trigger signal, the device specifically saves a sequence that covers the period before and after the event, making it easier to quickly analyze the cause. Designed for harsh industrial environments, the camera uses this method to ensure lean data streams and can be installed flexibly thanks to its large field of view.

Dimensions



Technical Data

General specifications		
Depth of focus		0.1 m ... infinite
Field of view		see table
Focal length		2.75 mm
Aperture		F2.2
Horizontal angle of view		102 °
Vertical angle of view		67 °
Filter		IR-filter
Recording duration		900 s
Nominal ratings		
Camera		

Release date: 2026-11-11 Date of issue: 2026-11-11 Filename: 70190086_eng.pdf

Technical Data

Type		CMOS
Chip size		7.4 mm diagonal
Shutter		Rolling shutter
Aspect ratio		16:9
Hardware		
Camera		
Image capture resolution		max. 4608x2592 (12 MP)
Video recording resolution		max. 1920x1080 (Full HD)
Focus		Motorized focus (adjustable via software) Autofocus
Memory		
Type/Size		eMMC / 8 GByte
Electrical specifications		
Operating voltage	U_B	18 ... 28 V DC
Internal input fuse		1.5 AT
Power consumption	P_0	max. 12 W Digital output Low
Interface		
Interface type		10 BASE-T/100 BASE-TX
Protocol		TCP/IP , HTTP / HTTPS , FTP , RTSP
Transfer rate		10 MBit/s / 100 MBit/s
Cable length		max. 100 m
IP address		DHCP activated , Fall back IP (192.168.100.50
Input		
Signal voltage		
High		16 ... 32 V DC
Low		0 ... 5 V DC
Input current		max. 7 mA
Trigger input		positive edge
Output		
Current	I_e	max. 200 mA
Voltage		< 1 ... 2 V under supply voltage (high) < 0.2 ... 0.3 V (low)
Protective function		short circuit protection
Directive conformity		
Electromagnetic compatibility		EN 61326-1:2013
Radio equipment		
Directive 2014/53/EU		ETSI EN 300330 V2.1.1
WEEE		
Directive 2012/19/EU		WEEE compliant
RoHS		
Directive 2011/65/EU (RoHS)		RoHS compliant
Conformity		
Shock resistance		EN 60068-2-27:2009
Playback formats		


Release date: 2026-11-11 Date of issue: 2026-11-11 Filename: 70190086_eng.pdf


Technical Data

Video	**Video Livestream:** - Codec/Container: H264/WebRTC - frame rate: 3 ... 24 fps - resolution: 1920 x 1080, 1280 x 720, 960 x 540, 640 x 360 **RTSP Stream:** - Codec/Container: H264/RTSP - frame rate: 3 ... 24 fps - resolution: 1920 x 1080, 1280 x 720, 960 x 540, 640 x 360 **HLS stream:** - Codec/Container: H264/HLS - frame rate: 3 ... 24 fps - resolution: 1920 x 1080, 1280 x 720, 960 x 540, 640 x 360 **Video Recording:** - Codec/Container: H264/MP4, adjustable quality - frame rate: 3 ... 24 fps - resolution: 1920 x 1080, 1280 x 720, 960 x 540, 640 x 360
Ambient conditions	
Operating temperature	-30 ... 50 °C (-22 ... 122 °F)
Storage temperature	-30 ... 50 °C (-22 ... 122 °F)
Relative humidity	non-condensing
Mechanical specifications	
Degree of protection	IP65
Connection	M12 x 1 connector, 4-pin, A-coded , unshielded (supply and digital input) M12 x 1 socket, 4-pin, D-coded , screened (Ethernet)
Material	
Housing	Die-cast aluminum alloy (GD-AlSi12)
Surface	black , powder coated
Observation window	glass, fully bonded
Mass	0.25 kg
Dimensions	
Height	104 mm
Width	81.2 mm
Depth	30 mm
Mounting	4x M6 1x ¼-20 UNC


Connection Assignment


Ethernet






Supply and digital input and output





Release date: 2026-11-11 Date of issue: 2026-11-11 Filename: 70190086_eng.pdf

Assembly



Technical Features

Field Of View

Distance	Horizontal field of view	Vertical field of view
0.5 m	1.235 m	0.662 m
1.0 m	2.470 m	1.324 m
2.5 m	6.174 m	3.309 m
5.0 m	12.349 m	6.619 m

Release date: 2026-11-11 Date of issue: 2026-11-11 Filename: 70190086_eng.pdf