



Inductive slot sensor

SC3,5-G-N0-Y70185030

- 3.5 mm slot width
- Usable up to SIL 2 acc. to IEC 61508

Dimensions





Technical Data

General specifications		
Switching function		Normally closed (NC)
Output type		NAMUR
Slot width		3.5 mm
Depth of immersion (lateral)		5 ... 7 mm , typ. 6 mm
Output type		2-wire
Nominal ratings		
Nominal voltage	U_o	8.2 V (R_i approx. 1 kΩ)
Operating voltage	U_B	5 ... 25 V
Switching frequency	f	0 ... 3000 Hz
Hysteresis	H	0.41 ... 0.6 mm
Suitable for 2:1 technology		yes , Reverse polarity protection diode not required
Current consumption		
Measuring plate not detected		≥ 3 mA
Measuring plate detected		≤ 1 mA
Switching state indicator		LED, yellow
Functional safety related parameters		


Release date: 2026-10-20 Date of issue: 2026-10-20 Filename: 70185030_eng.pdf

Technical Data

Safety Integrity Level (SIL)		SIL 2
$MTTF_d$		5880 a
Mission Time (T_M)		20 a
Diagnostic Coverage (DC)		0 %
Compliance with standards and directives		
Standard conformity		
NAMUR		EN 60947-5-6:2000 IEC 60947-5-6:1999
Electromagnetic compatibility		NE 21:2007
Standards		EN IEC 60947-5-2
Approvals and certificates		
IECEx approval		
Equipment protection level Ga		IECEx PTB 11.0091X
Equipment protection level Gb		IECEx PTB 11.0091X
Equipment protection level Da		IECEx PTB 11.0091X
Equipment protection level Mb		IECEx PTB 11.0091X
ATEX approval		
Equipment protection level Ga		PTB 99 ATEX 2219 X
Equipment protection level Gb		PTB 99 ATEX 2219 X
Equipment protection level Da		PTB 99 ATEX 2219 X
UL approval		cULus Listed Load Type: Resistive Circuitry: Class 2 Power Source Enclosure Type Rating: Type 1 Supply/Switching Voltage: 8.2 V DC
Ordinary Location		E87056
Hazardous Location		E501628
Control drawing		116-0453
CCC approval		
Hazardous Location		2020322315002306
KCC approval		
Hazardous Location		13-AV4BO-0353X
Marine approval		DNVGL TAA00001A5
Ambient conditions		
Ambient temperature		-25 ... 100 °C (-13 ... 212 °F)
Mechanical specifications		
Connection type		flexible leads
Housing material		PBT
Degree of protection		IP67
Cable		
Wire end ferrules		yes
Cable diameter		1.1 mm ± 0.1 mm
Bending radius		> 10 x cable diameter
Material		PVC
Number of cores		2
Core cross section		0.14 mm^2
Length	L	180 mm
Dimensions		
Height		15 mm
Width		10 mm
Length		19.5 mm
General information		
Use in the hazardous area		see instruction manuals

Release date: 2026-10-20 Date of issue: 2026-10-20 Filename: 70185030_eng.pdf

Connection Assignment



Release date: 2026-10-20 Date of issue: 2026-10-20 Filename: 70185030_eng.pdf