



Connecting Cable

V45-G-C5-GN1,8M-PUR-E1S-V45-G

- Hard-wearing PUR cable
- Suitable for robotic applications / torsion resistant
- Suitable for drag chains and abrasion resistant
- Industrial Ethernet
- Conforms to PROFINET
- CAT5/CAT5e cable
- Free of paint wetting interfering substances
- Halogen-free

Ethernet bus cable RJ45 to RJ45 PROFINET-coded, 4-pin, PUR cable green, Cat5e, shielded, drag-chain-suitable, torsion resistant

Dimensions



Technical Data

General specifications		
Connector 1		
Connection		plug
Construction type		RJ45
Style		straight
Locking		snap locking
Number of pins		8
Coding		PROFINET
Connector 2		
Connection		plug
Construction type		RJ45
Style		straight
Locking		snap locking
Number of pins		8
Coding		PROFINET
Electrical specifications		
Operating voltage	U_B	max. 48 V AC / 60 V DC
Insulation resistance		min. 100 MΩ
Conformity		
Degree of protection		EN 60529
Plug connection		connector RJ45 : IEC 60603-7
Component category		CAT5 (IEC 11801) , CAT5e (IEC 61156-6)
Flammability		IEC 60332-1-2 / UL 2556 / ISO 6722-1 5.22 (UN ECE-R 118.01)


Release date: 2026-11-10 Date of issue: 2026-11-10 Filename: 70186772_eng.pdf

Technical Data

Ambient conditions		
Ambient temperature		
Cable, fixed installation		-30 ... 70 °C (-22 ... 158 °F) , UL: -20 ... 70 °C (-4 ... 158 °F)
Cable, flexing		-20 ... 70 °C (-4 ... 158 °F)
Mechanical specifications		
Plug connector		
Loosening protection		available
Mating cycles		min. 100
Shielding		shield connected to connector
Degree of protection		IP20
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 5
Sheath diameter		6 mm
Bending radius		> 10 x cable diameter, movable installation > 8 x cable diameter, fixed installation
Sheath stripping force		max. 60 N / 100 mm
Sheath color		green (similar to RAL 6018)
Number of cores		4
Core cross section		0.34 mm² / 22 AWG
Cores color		Core 1: yellow Core 2: orange Core 3: white Core 6: blue
Core construction		7 x 0.254 mm Ø twisted quad
Shield		aluminum-lined polyester foil Tinned copper braiding
Length	L	1.8 m
Drag chain suitability		
Drag chain cycles		max. 1000000
Motion velocity		max. 3 m/s
Traverse distance		max. 5 m
Acceleration		max. 2 m/s²
Torsion cycles		min. 1000000
Torsional stress		± 180 °/m
Torsion velocity		35 cycles/min.
Mass		110 g
Material		
PWIS free		yes
Halogen-free		yes
Plug connector		
Body		PA, green
Flammability		V-0
Cable		
Sheathing		PUR based on polyether
Core insulation		PP
Flammability		FT2 complies with UN ECE-R 118.01

Release date: 2026-11-10 Date of issue: 2026-11-10 Filename: 70186772_eng.pdf

Connection Assignment



Release date: 2026-11-10 Date of issue: 2026-11-10 Filename: 70186772_eng.pdf