Safety light grid

LIGI


LG01B-2250-22C-5-R1-C3-F05-S15



- Cost-optimized series for standard tasks
- High degree of protection (IP67)
- Direct assembly
- Relay output

SSR safety light grid

Dimensions



Technical Data

General specifications		
Effective detection range		1.6 ... 10 m
Threshold detection range		14 m

Release date: 2025-10-17 Date of issue: 2025-10-17 Filename: 70192902_eng.pdf

Technical Data

Number of protective field beams		22
Light source		IRED
Light type		infrared
Marking		CE
Target size		50 ... 200 mm
Protection field height		2250 mm
Opening angle		eff. 5 °
Optical face		frontal
Ambient light limit		100000 Lux
Indicators/operating means		
Operation indicator		Emitter: LED green Receiver: LED green
Function indicator		Emitter: yellow LED Receiver: LED red: lit when the light beam is interrupted LED green: lights up when light beam is free
Stability alarm indicator		available
Electrical specifications		
Operating voltage	U_B	10 ... 30 V DC
Operating current	I_B	Emitter: approx. 30 mA (24 V) receiver: approx. 20 mA (24 V)
Power consumption	P_0	approx. 1.2 W
Input		
Test input		high active or low active
Output		
Output type		relay
Switching type		light-on
Signal output		100 mA , short-circuit protected , potential-free
Energized/De-energized delay		< 800 ms
Response time		≤ 100 ms
Conformity		
Product standard		EN ISO 13849 , EN 12978 , EN 61000-6-2, EN 61000-6-3
Ambient conditions		
Ambient temperature		-20 ... 60 °C (-4 ... 140 °F)
Storage temperature		-30 ... 70 °C (-22 ... 158 °F)
Relative humidity		max. 95 %, not condensing
Mechanical specifications		
Degree of protection		IP67 according to EN 60529
Connection		fixed cable with M8 plug, 6-pin
Material		
Housing		black anodized aluminum Epoxy resin molded
Mass		approx. 1450 g
Dimensions		
Height		2370 mm
Width		16 mm
Depth		16 mm

Release date: 2025-10-17 Date of issue: 2025-10-17 Filename: 70192902_eng.pdf