


Inductive slot sensor


SJ3,5-N-Y046116



- 3.5 mm slot width
- Spacer rubber NRB60 in black



Dimensions



Technical Data

General specifications

Switching function	Normally closed (NC)
Output type	NAMUR
Slot width	3.5 mm
Depth of immersion (lateral)	5 ... 7 mm , typ. 6 mm
Output type	2-wire

Nominal ratings

Nominal voltage	U_o	8.2 V (R_i approx. 1 k Ω)
Operating voltage	U_B	5 ... 25 V
Switching frequency	f	0 ... 3000 Hz
Hysteresis	H	0.41 ... 0.6 mm
Suitable for 2:1 technology		yes , Reverse polarity protection diode not required
Current consumption		
Measuring plate not detected		≥ 3 mA at nominal voltage
Measuring plate detected		≤ 1 mA at nominal voltage

Safety-relevant product characteristics

MTTF _d	8415 a
Mission Time (T_M)	20 a
Diagnostic Coverage (DC)	0 %

Release date: 2026-06-23 Date of issue: 2026-06-23 Filename: 70203989_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Compliance with standards and directives

Standard conformity		
NAMUR		EN 60947-5-6:2000 IEC 60947-5-6:1999
Standards		EN IEC 60947-5-2

Approvals and certificates

IECEx approval		
Equipment protection level Ga		IECEx PTB 11.0091X
Equipment protection level Gb		IECEx PTB 11.0091X
Equipment protection level Da		IECEx PTB 11.0091X
Equipment protection level Mb		IECEx PTB 11.0091X
ATEX approval		
Equipment protection level Ga		PTB 99 ATEX 2219 X
Equipment protection level Gb		PTB 99 ATEX 2219 X
Equipment protection level Da		PTB 99 ATEX 2219 X
UL approval		cURus Recognized Load Type: General Purpose Circuitry: Class 2 Power Source Supply/Switching Voltage: 8.2 V DC Further UL information see section "Additional Information"

Ambient conditions

Ambient temperature		-25 ... 100 °C (-13 ... 212 °F)
---------------------	--	---------------------------------


Mechanical specifications

Connection type		flexible leads LiY
Housing material		PBT
Degree of protection		IP67
Cable		
Cable diameter		1.1 mm ± 0.1 mm
Bending radius		> 10 x cable diameter
Material		PVC
Core cross section		0.14 mm ²
Length	L	500 mm
Dimensions		
Height		15 mm
Width		10 mm
Length		19.5 mm

General information

Use in the hazardous area		see instruction manuals
---------------------------	--	-------------------------

Connection Assignment



Technical Features

Additional UL Information

Conditions of Acceptability:

Suitability of the mounting means shall be determined in the end use application. The suitability of connection between supply connection and the end connector shall be determined in the end-use application.

The supply connections for these devices are intended for factory wiring only.

These devices shall be used within their recognized electrical ratings.

These proximity switches are intended to be powered by Listed Class 2 power supply or are located in a limited voltage / limited current circuit.