


Retroreflective sensor

OBS 10M-30GM90-E02



- Rugged housings withstand harsh environments
- Cable connection
- Polarization filter allows detection of shiny objects
- Tempered glass lens cover and Viton seals resist harsh environments
- Sensing range 10 m

30 mm Diameter Series



Technical Data

General specifications

Detection range	10 meters
Light source	Visible red LED 680 nm
Polarization filter	yes
Ambient light limit	≤ 100000 Lux
Hysteresis	H ≤ 15%

Indicators/operating means

Function indicator	dark on
--------------------	---------

Electrical specifications

Operating voltage	U_B	10 ... 30 V DC
No-load supply current	I_0	≤ 50 mA
Operating current	I_B	NPN, 250 mA / PNP, 100 mA
Protection class		IP68

Output

Switching type	light/dark on	
Signal output	1 NPN and 1 PNP	
Voltage drop	U_d	NPN, ≤2.0 V / PNP, ≤2.8 V
Switching frequency	f	250 Hz
Response time		≤ 2 ms

Standard conformity

Standards	EN 60947-5-2
-----------	--------------

Approvals and certificates

Approvals	CE
-----------	----

Ambient conditions

Ambient temperature	-40 ... 55 °C (-40 ... 131 °F)
Storage temperature	-40 ... 55 °C (-40 ... 131 °F)

Mechanical specifications

Degree of protection	IP68
Connection	2 meter CPE cable
Material	
Housing	Stainless steel 1.4305 / AISI 303
Optical face	Tempered glass
Mass	227 g

Release date: 2020-09-15 Date of issue: 2020-09-15 Filename: 903384_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS