



Thru-beam sensor emitter MD17/115b



- Emitter
- Compact, versatile housing
- 360° high visibility LEDs
- Pigtail quick disconnect
- M12 male connector

Thru-beam sensor transmitter, small design, infrared light, 20 m range, cable with M12 plug










Function

The ML17 sensor family offers diverse connection and installation options, which means that it can adapt to the most varied automation tasks. In addition to the usual fitting method using M4 screws, these sensors can also be installed by means of M18 threaded insert. All devices are equipped with a green Power On display and a yellow function display. These displays are arranged in such a way that they are clearly visible from different directions.

Dimensions










Technical Data

| System components | | |
|--------------------------------|----------------|--|
| Emitter | | MD17/115b |
| Receiver | | MV17/115b/136 |
| General specifications | | |
| Effective detection range | | 0 15 m |
| Threshold detection range | | 20 m |
| Reference target | | receiver |
| Light source | | IRED |
| Light type | | Infrared LED |
| Ambient light limit | | ≤ 10000 Lux |
| Indicators/operating means | | |
| Operation indicator | | LED green |
| Electrical specifications | | |
| Operating voltage | U_B | 10 30 V DC , class 2 |
| Ripple | | max. 10 % |
| No-load supply current | I_0 | < 25 mA |
| Operating current | I _B | |
| Time delay before availability | t_v | ≤ 200 ms |
| Conformity | | |
| Product standard | | EN 60947-5-2 IEC 60947-5-2 |
| Approvals and certificates | | |
| CE conformity | | CE |
| EAC conformity | | TR CU 020/2011 |
| UL approval | | cULus |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | |
| Ambient temperature | | -20 55 °C (-4 131 °F) |
| Storage temperature | | -20 70 °C (-4 158 °F) |
| Mechanical specifications | | |
| Housing width | | 15 mm |
| Housing height | | 34.5 mm |
| Degree of protection | | IP67 |
| Connection | | 150 mm cable with M12 connector, 4-pin |
| Material | | |
| Housing | | ABS |
| Optical face | | Acrylic |
| Mass | | 23 g |

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue) |
| 4 | BK | (black) |


Indication



1 Operating display green

Characteristic Curve





Matching System Components

| | MV17/115b/136 | Thru-beam sensor receiver, small design, infrared, light-on/dark-on switching, push-pull output, cable with M12 plug |
|--|---------------|--|
|--|---------------|--|

Accessories

| OMH-ML17 | Mounting bracket |
|-----------------|---|
| OMH-ML17-1 | Mounting bracket |
| V1-G-BK2M-PUR-U | Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant |
| V1-W-BK2M-PUR-U | Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant |
| V1-G-BK5M-PUR-U | Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant |
| V1-W-BK5M-PUR-U | Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant |