

Thru-beam sensor receiver MV17/115b/136



- Receiver
- Compact, versatile housing
- 360° high visibility LEDs
- 4-in-1 output (push-pull)
- Pigtail quick disconnect
- M12 male connector

Thru-beam sensor receiver, small design, infrared, light-on/dark-on switching, push-pull output, cable with M12 plug










Function


The ML17 sensor family offers diverse connection and installation options, which means that it can adapt to the most varied automation tasks. In addition to the usual fitting method using M4 screws, these sensors can also be installed by means of M18 threaded insert. All devices are equipped with a green Power On display and a yellow function display. These displays are arranged in such a way that they are clearly visible from different directions.

Dimensions










Technical Data

System components		
Emitter		MD17/115b
Receiver		MV17/115b/136
General specifications		
Effective detection range		0 15 m
Threshold detection range		20 m
Reference target		emitter
Light source		IRED
Light type		Infrared LED
Ambient light limit		≤ 10000 Lux
Indicators/operating means		3 10000 Eux
Operation indicator		LED green
Function indicator		LED yellow, lights up with receiver lit
Electrical specifications		LED yellow, lights up with receiver lit
Operating voltage	U _B	10 20 V DC class 2
Ripple	ΟB	10 30 V DC , class 2 max. 10 %
		< 25 mA
No-load supply current	l ₀	
Operating current	I _B	100 mA max per output
Time delay before availability	t _v	≤ 200 ms
Output		P 1971 1
Switching type		light/dark on
Signal output		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U _d	≤2 V DC
Switching frequency	f	150 Hz
Response time		≤ 3 ms
Conformity		
Product standard		EN 60947-5-2 IEC 60947-5-2
Approvals and certificates		
CE conformity		CE
EAC conformity		TR CU 020/2011
UL approval		cULus
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 55 °C (-4 131 °F)
Storage temperature		-20 70 °C (-4 158 °F)
Mechanical specifications		
Housing width		15 mm
Housing height		34.5 mm
Degree of protection		IP67
Connection		150 mm cable with M12 connector, 4-pin
Material		
Housing		ABS
Optical face		Acrylic
Optical face		

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)


Indication



1	Signal display	yellow
2	Operating display	green

Characteristic Curve





Matching System Components

MD17/115b	Thru-beam sensor transmitter, small design, infrared light, 20 m range, cable with M12 plug

Accessories

OMH-ML17	Mounting bracket
OMH-ML17-1	Mounting bracket
V1-G-BK2M-PUR-U	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant
V1-W-BK2M-PUR-U	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant
V1-G-BK5M-PUR-U	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant
V1-W-BK5M-PUR-U	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant

Additional Information

4-in-1 Output

The 4-in-1 output automatically detects the connected load, so the output either sources or sinks current depending on the load. The light on/dark on switch on the housing selects normally open or normally closed mode. A single sensor can operate as NPN normally open, NPN normally closed, PNP normally open, or PNP normally closed.



FPEPPERL+FUCHS