



## PC Workstation VisuNet Edge PC8722


- Extended temperature range for indoor/outdoor use
- Modular design for field maintainability
- Solution for General Purpose and Div. 2
- Variety of keyboard and mounting options
- Watershed housing allows for proper drainage
- Windows 7 Ultimate (32-bit or 64-bit)
- Widescreen 16:10 aspect ratio



### Function

The VisuNet Edge is a universal design that is well suited for many applications. Specifically designed for manufacturing environments where dust, bacteria, water, and other undesirable materials might accumulate, the sloped enclosure provides washdown solutions with proper drainage to prevent standing water. The formed lip enclosure opening prevents the flow of liquid or other contaminants from entering the enclosure. The watershed enclosure with extended keyboard housing is available as a complete stand-alone PC workstation with different mounting options available: pedestal or wall mount.

### Dimensions



### Technical Data

#### Hardware

Processor	Intel® Core™ i7-3517UE 1.7 GHz or Intel® Atom™ E3826 1.46 GHz
RAM	up to 8 GB
Mass storage	120 GB SSD

#### Supply

Release date: 2023-11-28 Date of issue: 2023-11-28 Filename: t159184\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

## Technical Data

Connection	Terminals
Power consumption	Intel® Atom™: max 60 W , 100 ... 240 VAC, 50 ... 60 Hz, or 20 ... 30 VDC Intel® Core™ i7: max 72 W , 100 ... 240 VAC, 50 ... 60 Hz, or 20 ... 30 VDC
<b>Indicators/operating means</b>	
Display	
Screen diagonal	22 inch (559 mm)
Response time	4 ms
Resolution	1680 x 1050
Color depth	24 bit (16.7 M) color
Contrast	1000:1
Brightness	250 cd/m <sup>2</sup> (nit)
Reading angle	160° in all directions
Life span	back lamp life: 50,000 hrs typical half life
Input devices	
Touchscreen	5-wire resistive
<b>Interface</b>	
Interface type	Intel® Core™ i7 : 1 GB ethernet, 2 x USB, audio, RS232, power Intel® Atom™ : 2 x 1 GB ethernet, 2 x USB, audio, RS232, power
<b>Directive conformity</b>	
Electromagnetic compatibility	
Directive 89/336/EEC	EN55022A, EN61000-6-2, EN61000-3-2, EN61000-3-3
<b>Software</b>	
Operating system	Windows 7 Ultimate (32-bit or 64-bit)
<b>Ambient conditions</b>	
Operating temperature	-20 ... 50 °C (-4 ... 122 °F)
Storage temperature	-20 ... 60 °C (-4 ... 140 °F)
Relative humidity	0 ... 90% (noncondensing)
<b>Mechanical specifications</b>	
Degree of protection	NEMA Type 4X
Material	304 (UNS S30400) stainless steel
Housing	304 (UNS S30400) stainless steel
Surface	#4, 180 grit
Mass	approx. 52.16 kg (115 lbs) Empty housing ; Varies with configuration
Dimensions	813 x 724 x 381 mm (32.0 x 28.5 x 15.0 inch) (sloping top) Volume: approx. 3.2 cu ft
Mounting	Wall or pedestal mount
<b>International approvals</b>	
UL approval	cULus
Approved for	General purpose Class I, Division 2, Groups A, B, C, and D

Release date: 2023-11-28 Date of issue: 2023-11-28 Filename: t159184\_eng.pdf

Release date: 2023-11-28 Date of issue: 2023-11-28 Filename: t159184\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

Type code

**P C 8 7 1 9 - A - G P - P D 1 A C W S 5 - C K 1 U S - S 0 - N**

**Options**

- N** No option
- Y** Custom, consult factory

**Special accessories**

- S0** No special accessories

**Keyboard layout**

- US** Keyboard, layout U.S.

**Keyboard / mouse version**

- K1** Foil keyboard, no mouse
- K4** Foil keyboard & capacitive touchpad mouse
- K6** Foil keyboard & joystick
- K8** Foil keyboard & 50 mm optical trackball mouse
- K9** Foil keyboard & resistive touchpad mouse

**Keyboard housing**

- C** Keyboard & mouse installed

**Housing / frontplate version**

- WS5** Piano style housing (stainless steel 304), wall mount, service opening on front, hinges on left, extended keyboard
- WS6** Piano style housing (stainless steel 304), pedestal mount, service opening on front, hinges on left, extended keyboard (pedestal not included - available as accessory)

**Power supply**

- AC** 90 ... 260 V AC, 50 ... 60 Hz
- DC** 24 V DC

**Connection**

- PD1** i7-3517UE 1.7 GHz, 4 GB RAM, 120 GB SSD, 2 x LAN, 4 x USB, Windows 7 Ultimate (32-bit)
- PE2** i7-3517UE 1.7 GHz, 8 GB RAM, 120 GB SSD, 2 x LAN, 4 x USB, Windows 7 Ultimate (64-bit)
- PF1** Atom E3826 1.46 GHz, 4 GB RAM, 120 GB SSD, 2 x LAN, 4 x USB, Windows 7 Ultimate (32-bit)
- PG2** Atom E3826 1.46 GHz, 8 GB RAM, 120 GB SSD, 2 x LAN, 4 x USB, Windows 7 Ultimate (64-bit)

**Protection**

- GP** Industrial, Non-EX
- D2** Class I, Div 2 Groups A, B, C, D

**Screen type**

- A** Antiglare glass front, non-touch
- R** Touch screen, resistive, 5-wire, hardened glass - "PC8719" option only
- T** Touch screen, resistive, 5-wire, intrinsically safe
- U** High-bright display, with touch screen, 5-wire resistive - "PC8719" option only
- F** High-bright display, non touch, antiglare - "PC8719" option only
- K** High-bright display, with touch screen, 5-wire hardened resistive - "PC8719" option only

**Monitor**

- PC8719** PC monitor, 19 in (483 mm), SXGA (1280 x 1024 pixels)
- PC8722** PC monitor, 22 in (559 mm), WSXGA (1680 x 1050 pixels)

Release date: 2023-11-28 Date of issue: 2023-11-28 Filename: t159184\_eng.pdf

Release date: 2023-11-28 Date of issue: 2023-11-28 Filename: t159184\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com