

AS-Interface splitter box

VAZ-T1-FK-G10-F-5M-PUR-V1-G




- One piece housing
- Simple and fast mounting
- Fuse with LED display
- Gold-plated and machined contacts
- Oil and abrasion resistant PUR line appropriate for drag chains
- Immunity to vibration
- Degree of protection IP68 / IP69K
- Halogen-free

G10 junction block, LED status indication, AS-Interface to 1x M12 round plug connector



Dimensions



Technical Data

General specifications

Construction type	Socket, straight Flat cable terminal AS-Interface
-------------------	--

Indicators/operating means

LED FAULT	LED red: Fuse unit blown
LED PWR	LED green: normal operation

Electrical specifications

Rated operating voltage	U_e	10 ... 32 V PELV
Protection class		III
Short-circuit current	I_k	max. 50 A
Surge protection		U_e : Over voltage category III, safe isolated power supplies (PELV)

Output

Current loading capacity		Rated current of the fuse: 1.6 A Continuous operation: 1.2 A
Voltage drop	U_d	≤ 0.4 V
Overload protection		Fuse acc. to UL248-1, UL248-14

Compliance with standards and directives

Directive conformity		
EMC Directive 2004/108/EC		EN 61000-6-2:2005, EN 61000-6-4:2007
Standard conformity		
Noise immunity		EN 61000-6-2:2005
Emitted interference		EN 61000-6-4:2007
Degree of protection		EN 60529:2000

Approvals and certificates

Release date: 2026-02-16 Date of issue: 2026-02-16 Filename: 70204149_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data


UL approval		cULus Listed, Type 1 enclosure
Application		for use in NFPA 79 applications
Maximum permissible operating voltage		max. 32 V
Maximum permissible operating current		max. 1.6 A
Maximum permissible ambient temperature		max. 55 °C (max. 131 °F)
UL File Number		E223772
Ambient conditions		
Ambient temperature		-25 ... 70 °C (-13 ... 158 °F)
Storage temperature		-25 ... 85 °C (-13 ... 185 °F)
Mechanical specifications		
Degree of protection		IP67 IP67 / IP68 / IP69K with flat cable VAZ-FK-S-*
Connection		Flat cable AS-Interface: cable piercing method Plug connection: M12 x 1 socket (V1)
Material		
Contacts		CuSn / Au
Housing		PBT PC
Body		PUR, black
Cable		PUR
Mounting screw		Stainless steel 1.4305 / AISI 303
Cable		
Sheath diameter		Ø4,3 mm
Color		black
Cores		2 x 0.34 mm²
Length	L	5 m
Mass		70 g
Tightening torque, fastening screws		1.65 Nm
Tightening torque, cable gland		0.4 Nm
Dimensions		
Height		22 mm
Width		27.7 mm
Length		40.5 mm
Note		The unused flat cable connector is closed with a seal.

Wiring Diagram




Release date: 2026-02-16 Date of issue: 2026-02-16 Filename: 70204149_eng.pdf

Assembly



- ① Operating display
AS-Interface
- ② Fuse blown
AS-Interface

Mounting



You may screw the device onto a level mounting surface using two M4 attachment screws. The attachment screws are not included.