



Retroreflective sensor with polarization filter



ML100-54/103/115

- Miniature design
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Very bright, highly visible light spot
- Full metal thread mounting
- Not sensitive to ambient light

Retroreflective sensor with polarization filter, plastic housing, 5 m detection range, red light, sensitivity adjuster, light/dark on, DC version, PNP output, fixed cable








Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions





Technical Data **General specifications** Effective detection range 0 ... 3.5 m Reflector distance 0.01 ... 3.5 m Threshold detection range 4.5 m Reference target H50 reflector LED Light source Light type modulated visible red light Polarization filter Diameter of the light spot approx. 350 mm at a distance of 4.5 m Opening angle approx. 4° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters MTTF_d 860 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted Function indicator Control elements sensitivity adjustment Control elements Light-on/dark-on changeover switch **Electrical specifications** U_{B} 10 ... 30 V DC Operating voltage Ripple max. 10 % No-load supply current lo < 20 mA Output Switching type The switching type of the sensor is adjustable. The default setting is: light-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC max. 100 mA, resistive load Switching current ≤ 1.5 V DC Voltage drop U_{d} 1000 Hz Switching frequency Response time 0.5 ms Conformity Product standard EN 60947-5-2 Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -30 ... 60 °C (-22 ... 140 °F) Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Housing width 11 mm Housing height 31 mm 20 mm Housing depth Degree of protection IP67 Connection 2 m fixed cable Material PC (Polycarbonate) Housing Optical face **PMMA** Mass approx. 50 g


Tightening torque, fastening screws

0.6 Nm


Technical Data

Cable length 2 m

Connection




Assembly




1	Light-Dark-switching		
2	Sensitivity adjuster		
3	Signal display	ay yellow	
4	Operating display	green	

Characteristic Curve



Characteristic Curve



Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
*	OMH-F10-ML100	Mounting aid for ML100 series
A SECTION ASSESSMENT	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
	OMH-10	Mounting aid for ML100 series
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole
	REF-H60-2	Reflector with mounting holes
	REF-H33	Reflector with screw fixing

Accessories OFR-70-2 Reflective tape 70 mm x 70 mm REF-MH23-2 Reflector with Micro-structure, rectangular 23 mm x 14 mm, diagonal mounting hole REF-H85-2 Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes REF-H50 Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap OFR-100/100 Reflective tape 100 mm x 100 mm