






### **Model Number**

NMB15-30GM55-Z4-C-300MM-V1

## **Features**

- 15 mm flush
- Stainless steel sensing face
- Increased operating distance
- **Weld Immune**

# Connection



# **Pinout**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	RK	(black)

# **Accessories**

2012-12-13 912723\_eng.xml

Date of issue:

2012-12-13 14:34

Release date:

V1-G-OR2M-POC

Female cordset, M12, 4-pin, TPE cable, welding-bead resis-

V1-G-2M-PUR

Cable socket, M12, 4-pin, PUR cable V1-W-2M-PUR


Cable socket, M12, 4-pin, PUR cable

Mounting aid

**AB-30** 

AB-30-L3M-C Mounting aid

### **Dimensions**



# **Technical Data**

\ I	
aenerai	specifications

acticiai specifications				
Switching element function		DC	NO	
Rated operating distance	s <sub>n</sub>	15 mm		
Installation		flush (Requi	irements: see drawing below	<b>'</b> )
Output polarity		DC		
Assured operating distance	sa	0 12.15 m	nm	
Actuating element		Ferrous and	d nonferrous targets	
Reduction factor r <sub>Al</sub>		0.4		
Reduction factor r <sub>Cu</sub>		0.2		
Reduction factor r <sub>304</sub>		0.85		
Reduction factor r <sub>St37</sub>		1		
Nominal ratings				

 $\mathsf{U}_\mathsf{B}$ 6 ... 30 V Operating voltage Switching frequency 5 Hz Н 5 ... 15 typ. 10 % Hysteresis Reverse polarity protection yes Short-circuit protection < 3 V DC Voltage drop

Operating current 2 ... 100 mA < 400 μA Off-state current Mag. Field strength, AC fields Mag. Field strength, DC fields Indicators/operating means 250 mT 250 mT

Operating display LED, red output

Ambient conditions

Ambient temperature 0 ... 70 °C (32 ... 158 °F)

Mechanical specifications

Connection type Cable connector M12 x 1 , 4-pin with TPE cable , 300 mm Xylan coated - Stainless steel 1.4305 / AISI 303 Xylan coated - Stainless steel 1.4305 / AISI 303 Housing material

Sensing face Protection degree IP67 / IP68 / IP69K - cordset dependent according to cable speci-

fication

# Compliance with standards and directives


Standard conformity Standards

EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval cULus Listed, General Purpose CSA approval cCSAus Listed, General Purpose

Products with a maximum operating voltage of  $\leq 36$  V do not bear a CCC marking because they do not require approval. CCC approval



Sensor face is flush with mounting surface.