


Inductive sensor


NMB6-F104M-E2-NFE



- Sensing range 6 mm
- Nonferrous targets
- Stainless steel sensing face
- PNP version



Dimensions



Technical Data

General specifications		
Switching function		Normally open (NO)
Output type		PNP
Rated operating distance	s _n	6 mm
Installation		flush
Assured operating distance	s _a	0 ... 4.86 mm
Actuating element		Nonferrous targets
Reduction factor r _{Al}		1
Reduction factor r _{Cu}		1.1
Reduction factor r ₃₀₄		0
Reduction factor r _{St37}		0
Reduction factor r _{Brass}		0.9
Output type		3-wire
Nominal ratings		
Operating voltage	U _B	10 ... 30 V DC
Switching frequency	f	20 Hz
Hysteresis	H	5 ... 15 typ. 10 %

Release date: 2025-04-09 Date of issue: 2025-04-09 Filename: 915189_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

Reverse polarity protection		reverse polarity protected
Short-circuit protection		yes
Voltage drop	U_d	$\leq 2 \text{ V}$
Operating current	I_L	$\leq 100 \text{ mA}$
Current consumption		$\leq 10 \text{ mA}$
Off-state current	I_r	$\leq 10 \mu\text{A}$
Indicators/operating means		
Operation indicator		LED red: Output (rear visible)
Standard conformity		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus Listed, General Purpose
CCC approval		CCC approval / marking not required for products rated $\leq 36 \text{ V}$
Ambient conditions		
Ambient temperature		$-25 \dots 70 \text{ }^\circ\text{C}$ ($-13 \dots 158 \text{ }^\circ\text{F}$)
Mechanical specifications		
Connection type		cable
Housing material		Stainless steel 1.4305 / AISI 303
Degree of protection		IP67
Cable		
Wire end ferrules		yes
Cable diameter		$4.8 \text{ mm} \pm 0.2 \text{ mm}$
Bending radius		$> 10 \times \text{cable diameter}$
Material		PUR
Color		black
Number of cores		3
Core cross section		0.34 mm^2
Length	L	2 m
Dimensions		
Height		8 mm
Width		20 mm
Length		32 mm

Connection

