



KVM Workstation

KM922 Series

- 22 inch TFT display w/ optional touch screen
- Widescreen 16:10 aspect ratio
- Seams continuously welded and ground smooth (Type 4/4X, IP66)
- Various keyboard/mouse options
- Connects to host PC via internal KVM extender
- Class I, Div. 2 / ATEX Zone 2 approved

22 inch (55.9 cm) industrial KVM monitor



Function


VisuNet IND KM922 rugged industrialized housing was made to extend the control room into the toughest process conditions. The KVM extender option allows the display and the host PC to be up to 400 m (1300 ft) apart and is certified for installation in Class I/Div 2 locations. Designed for manufacturing environments where dust, bacteria, water, and other undesirable materials might accumulate, the enclosure construction and surfaces provide wash down solutions proper drainage to prevent standing water and easily mounts utilizing the industry standard 100 mm VESA.

This 22" monitor features an optional touch screen, keyboard with various mouse options, and choice of one of three KVM types.


Connection

SP7 / SS7

CAT5 Terminals	Description
1.1	BI_DA + WH/GN
1.2	BI_DA - GN
1.3	BI_DB + WH/OR
1.4	BI_DC + BU
1.5	BI_DC - WH/BU
1.6	BI_DB - OR
1.7	BI_DD + WH/BN
1.8	BI_DD - BN




Fiber



CAT5

SP5 / SS5



Fiber



CAT5

Release date: 2023-05-23 Date of issue: 2023-05-23 Filename: t159321_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com


USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Dimensions



Release date: 2023-05-23 Date of issue: 2023-05-23 Filename: t159321_eng.pdf

Technical Data

General specifications	
Distance	Transmitter "K4": 120 m (400 ft) Transmitter "K5": 200 m (650 ft), 62.5 μ multimode; 400 m (1300 ft), 50.0 μ multimode
Supply	
Connection	Monitor: power, CAT5, fiber (LC)
Power consumption	Main unit: 50 ... 60 Hz; 20-30 VDC Transmitter "K4": 5 VDC @ 10 W, max Transmitter "K5": 5 VDC @ 10 W, max
Indicators/operating means	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Technical Data


Indicators		Transmitter "K4": video check LED; front panel - power Transmitter "K5": video check LED; front panel - power
Display		
Screen diagonal		22 inch (559 mm)
Response time		4 ms
Resolution		1680 x 1050
Color depth		24 bit (16.7 M) color
Contrast		1000:1
Brightness		250 cd/m ² (nit)
Reading angle		160° in all directions
Life span		back lamp life: 50,000 hrs typical half life
Input devices		Transmitter "K4": 29-pin DVI-D; 2 x USB Type B (keyboard, mouse/touchscreen); 1 x RS232 (touchscreen); 1 x RJ45 (CAT5e/6) Transmitter "K5": 29-pin DVI-D; 1 x USB Type B (keyboard, mouse/touchscreen); 1 x RS232 (touchscreen); fiber optic (multimode) LC connectors
Touchscreen		5-wire resistive
Keyboard		touchpad , optical trackball (50 mm) , joystick
Serial data		
Baud rate		19.2 KBd max
Flow control		RTS, CTS, DTR, DSR
Directive conformity		
Electromagnetic compatibility		
Directive 89/336/EEC		EN55022A, EN61000-6-2, EN61000-3-2, EN61000-3-3
Ambient conditions		
Operating temperature		-20 ... 45 °C (-4 ... 113 °F)
Storage temperature		-20 ... 60 °C (-4 ... 140 °F)
Relative humidity		0 ... 90% (noncondensing)
Shock resistance		30g, 11 ms, all axis
Vibration resistance		5 ... 100 Hz 1G, 12 m/s ²
Mechanical specifications		
Degree of protection		Type 4X (stainless steel) Type 4 (painted steel) IP66
Material		Main enclosure: painted black steel or 316L stainless steel Main enclosure (rear cover): 6062 anodized aluminum, marine grade
Installation		100 mm (3.9 inch) VESA mount
Mass		Main unit: 15.9 kg (35 lb) without keyboard; 21.3 kg (47 lb) with keyboard Transmitter "K4": 0.3 kg (0.7 lbs) Transmitter "K5": 0.3 kg (0.7 lbs)
Dimensions		Main enclosure: 636 x 406 x 86 mm (25.0 x 16.0 x 3.4 inch), junction box adds 43 mm (1.7 inch) to depth Keyboard enclosure: 559 x 254 x 51 mm (22.0 x 10.0 x 2.0 inch) Transmitter "K4": 104 x 135 x 36 mm (4.1 x 5.3 x 1.4 inch) Transmitter "K5": 104 x 135 x 36 mm (4.1 x 5.3 x 1.4 inch)
Data for application in connection with hazardous areas		
EU-type examination certificate		
Marking		Ⓔ II 3G Ex ic nA IIC T4 Gc
International approvals		
ETL approval		Class I, Div. 2 Groups A, B, C, D; T4

Accessories

	VESA CABLE FEEDTHROUGH	Slimline adapter plate
---	-------------------------------	------------------------

Type Code

K M 9 2 2 T - D 2 - K 5 A C - S S 7 N K 0 L 0 - S 0 - N



Options
N No options

Special accessories
S0 No special accessories

Keyboard layout
L0 No keyboard, no layout
US Keyboard, layout U.S.

Keyboard/mouse version
K0 No keyboard, no mouse
K4 Foil keyboard & capacitive touchpad mouse
K6 Foil keyboard & joystick
K8 Foil keyboard & 50 mm optical trackball mouse
K9 Foil keyboard & resistive touchpad mouse

Keyboard housing
N No keyboard, no mouse
C Hinge mounted

Housing version
SP5 IND housing, black painted steel, rear junction box with IP67 connectors - "GP" Protection only
SS5 IND stainless steel (316L) housing, rear junction box with IP67 connectors - "GP" Protection only
SP7 IND housing, black painted steel, rear junction box with cable glands
SS7 IND stainless steel (316L) housing, rear junction box with cable glands

Power supply
DC 24 V DC

Board specifications
K4 KVM for DVI-D video included, 2x USB interface, 1x RS232, CATx cable transmission
K5 KVM for DVI-D video included, 2x USB interface, 1x RS232, fiber-optic transmission (multi-mode), 2x LC connectors

Protection
V3 Class I, Div. 2 Groups A, B, C, D / ATEX Zone 2
GP Industrial, Non-EX
D2 Class I, Div. 2 Groups A, B, C, D

Screen type
A Antiglare glass front, non-touch
T Touch screen, resistive, 5-wire

KM922 KVM monitor, 22 in (559 mm), SXGA (1680 x 1050 pixels), internal KVM

Release date: 2023-05-23 Date of issue: 2023-05-23 Filename: t159321_eng.pdf