



Thru-beam sensor M41/MV41/25/70/76a/136



- Rugged series in corrosion-resistant metal housing
- Long sensor range with high power mode
- Resistant against noise: reliable operation under all conditions
- Clear and functional display concept for the operating modes
- Aluminum housing with high quality Delta-Seal coated
- Scratch-resistant and solvent resistant glass lens

Robust thru-beam sensor, compact housing design, 16 m detection range, emission frequency F1, red light and infrared light, light on, 2 push-pull outputs, test input, M9 plug







Function


The unique and extremely popular design of the MLV41 series enables it be mounted correctly in confined areas and offers all the functions that are normally only found on larger phototelectric sensors. The MLV41 series comes with a range of functions. For example, highly visible status LEDs on the front and back, resistance to ambient light, crosstalk protection and universally applicable output stages that permit every possible switching logic and polarity to be realized. The enhanced resistance to ambient light ensures reliable operation even where modern energy-saving lamps with electronic ballasts are in use. The same applies where multiple devices are present, i.e. the use of a number of sensors in the same vicinity causes no problems.

Dimensions












Technical Data

System components	
Emitter	M41/70/76a
Receiver	MV41/25/70/136
General specifications	
Effective detection range	0 16 m
Threshold detection range	normal mode: 25 m High power mode: 35 m (Control input at UB+)
Light source	normal mode: LED High power mode: LED+IRED
Light type	normal mode: modulated visible red light High power mode: Red and infrared, modulated light
Diameter of the light spot	approx. 500 mm at detection range 16 m
Opening angle	approx. 1.5 °
Optical face	frontal
Ambient light limit	50000 Lux
Functional safety related parameters	
MTTF _d	844 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green: power on
Function indicator	Receiver: LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve; OFF when light beam is interrupted
Control elements	sensitivity adjustment (receiver)

Electrical specifications

Technical Data Operating voltage U_{B} 10 ... 30 V DC, class 2 max. 10 % Ripple max. 30 mA No-load supply current Input Test input emitter deactivation at +U_B (emitter) High power mode activation with +UB (emitter) Control input Output Switching type light-on Signal output 2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected Switching voltage max. 30 V DC Switching current max. 100 mA $U_{\text{d}} \\$ ≤ 2.5 V DC Voltage drop Switching frequency 1000 Hz Response time 0.5 ms Compliance with standards and directives Directive conformity EMC Directive 2004/108/EC EN 60947-5-2:2007 Standard conformity Product standard EN 60947-5-2:2007 IEC 60947-5-2:2007 Standards **UL 508** Approvals and certificates **UL** approval cULus Listed, Class 2 Power Source, Type 1 enclosure CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) -40 ... 75 °C (-40 ... 167 °F) Storage temperature **Mechanical specifications** Housing width 31 mm Housing height 56.5 mm Housing depth 13.6 mm Degree of protection IP67 Connection with M9, 5-pin metal connector Material Aluminum, Delta-Seal coated Housing Optical face glass pane Connector metal Mass 50 g (device)



- O = Light on
- = Dark on


Connection Assignment





Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)

Assembly









Accessories

ОМН-09	Mounting bracket for Sensors series MLV41 for M12 rod mounting
OMH-40	Mounting bracket