

## 6500 Series Vent

### EPV-6500-\*-\*

- A selection of vents for specific applications
- Intrinsically safe operation
- Continuous flow vents for precise flow rates for dilution applications
- Continuous flow measurement for dilution, purging, and pressurization
- Low leakage rate vents for air or inert gas conversation
- High flow rate vents for fast, large enclosure systems
- Universal mounting in any orientation including most of the unit inside the enclosure
- Maximum enclosure size 12.75 cu.meters (450 cu.ft.)
- ATEX/IECEX Zone 1/21 certified for Ex pyb and Ex pxb
- Up to SIL 2 acc. to IEC/EN 61508


Enclosure protection vent for 6500 series type Ex pyb Ex pxb purge and pressurization system



### Function


EPV-6500-\*-\* enclosure protection vents provide pressure relief to pressurized enclosures and pressure and flow information to 6500 series control units. The vents are intrinsically safe when used in conjunction with a 6500 control unit. Vent models are available for standard applications or continuous flow dilution applications that require precise flow measurement. For a streamlined enclosure design, the vent can be mounted in any orientation and can be mounted inside a pressurized enclosure with just the vent cap outside of the enclosure. EPV-6500-SS-\* models include reference pressure tubing and hardware for internal mounting.

### Connection



	4-PIN
1	+ (brown)
2	A (white)
3	- (blue)
4	B (black)

## Dimensions



## Technical Data

### General specifications

Series	6500
Number of volume exchanges	5 to 19
Hazardous environment	gas, dust, gas and dust

### Functional safety related parameters

Safety Integrity Level (SIL)	SIL 2
------------------------------	-------

### Electrical specifications

Connection	
Signal	BUS back to the 6500 control unit
Connection	M12 connector, 4-pin, cable length 5 meters (provided)
Cable length	max. 60 meters at 50 pf/ft and 0.2 $\mu$ H/ft

### Indicators/settings

LED indication	POWER: green
----------------	--------------

### Pneumatic parameters

Protective gas supply	instrument grade air or inert gas
Maximum pressure	depends on the integrity of the enclosure (strength) max. vent pressure: 25" wc (635 mm wc) (62 mbar / 6200 pa) vent pressure range: 0 to 9.9" wc (0 to 25 mbar)
Safe pressure	Gas: 0.35" wc (8,88 mm wc) (0.88 mbar/ 88 pa) Dust: 0.35" wc (8,88 mm wc) (0.88 mbar/ 88 pa) Gas+Dust: 0.35" wc (8,88 mm wc) (0.88 mbar/ 88 pa)

Release date: 2023-01-20 Date of issue: 2023-01-20 Filename: t179721\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

Purge flow rate	See graphs Readout on display is in increments of 28 l/min (1 scfm). Minimum and maximum reading depends on type of vent and supply pressure. EPV-6500*-07, 08 will readout continuous flow.
Purge flow and enclosure pressure rate	See graphs Readout on display is in increments of 28 l/min (1 scfm). Minimum and maximum reading depends on type of vent and supply pressure. EPV-6500*-07, 08 will readout continuous flow.
Flow rate for leakage compensation	EPV-6500....-01: 593 l/hr (21 scfh) @ .63mbar (.25"wc) 1640 l/hr (58 scfh) @ 1.9mbar (0.75"wc) EPV-6500....-03: 395 l/hr (14 scfh) @ .63mbar (.25"wc) 961 l/hr (34 scfh) @ 1.9mbar (0.75"wc) EPV-6500....-05: 260 l/hr (9.2 scfh) @ .63mbar (.25"wc) 622 l/hr (22 scfh) @ 1.9mbar (0.75"wc) EPV-6500....-07: n/a EPV-6500....-08: n/a
Breaking pressure	EPV-6500....-01: 2.0 mbar (0.8" wc) EPV-6500....-03: 3.5 mbar (1.4" wc) EPV-6500....-05: 3.8 mbar (1.5" wc) EPV-6500....-07: n/a EPV-6500....-08: n/a
<b>Conformity</b>	
Degree of protection	EN 60529
Shock resistance	EN 60068-2
<b>Ambient conditions</b>	
Ambient temperature	-20 ... 70 °C (-4 ... 158 °F)
Storage temperature	-40 ... 70 °C (-40 ... 158 °F)
Relative humidity	5 ... 90 %, non-condensing
Vibration resistance	5 ... 100 Hz , 1 g, 12 m/s <sup>2</sup> , all axes
Impact resistance	30 g, 11 ms, all axes
<b>Mechanical specifications</b>	
Degree of protection	IP66
Material	EPV-6500-AA-.... Cap: marine grade 5052 anodized aluminum, marine grade 6061T6 anodized aluminum EPV-6500-SS-.... Cap: 316L (UNS S31603) stainless steel; Body: marine grade 6061T6 anodized aluminum
Spark arrestor	304 (UNS S30400) stainless steel
Installation	- any orientation to enclosure - not gravity dependent - internal and external mounting possible
Mass	approx. 1.4 kg (3.1 lb)
Dimensions	127 x 146 x 83 mm (5.0" x 5.8" x 3.3")
Mounting	1 ½" NPT knockout (50.8mm (2") hole) with seal nut included
<b>Data for application in connection with hazardous areas</b>	
EU-type examination certificate	DEMKO 15 ATEX 1622X
Marking	⊕ II 2G Ex ib [pxb Gb] IIC T4 Gb ⊕ II 2D Ex ib [pxb Db] IIIC T135 °C Db ⊕ II 2G Ex ib [pyb Gb] IIC T4 Gb ⊕ II 2D Ex ib [pyb Db] IIIC T135 °C Db
<b>Directive conformity</b>	
Directive 2014/34/EU	EN IEC 60079-0:2018 , EN 60079-2:2014 , EN 60079-11:2012
<b>International approvals</b>	
IECEx approval	
IECEx certificate	IECEx UL 15.0147X

Release date: 2023-01-20 Date of issue: 2023-01-20 Filename: t179721\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data


IECEX marking	<p>Ex ib [pxb Gb] IIC T4 Gb  Ex ib [pxb Db] IIIC T135 °C Db  Ex ib [pyb Gb] IIC T4 Gb  Ex ib [pyb Db] IIIC T135 °C Db  EPV-6000: <math>-20\text{ °C} \leq T_{\text{amb}} \leq 60\text{ °C}</math>  EPV-6500: <math>-20\text{ °C} \leq T_{\text{amb}} \leq 70\text{ °C}</math></p>
<b>General information</b>	
Supplementary information	<p>EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see <a href="http://www.pepperl-fuchs.com">www.pepperl-fuchs.com</a>.</p>

**Characteristic Curve**


**Flow Rate Curves**

**Standard Vent Pressure / Flow Curves**


EPV-6500-\* -01



EPV-6500-\* -03



EPV-6500-\* -05




Release date: 2023-01-20 Date of issue: 2023-01-20 Filename: t179721\_eng.pdf


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

**Continuous Vent Pressure / Flow Curves**

EPV-6500-\*-07: 8 mm Orifice



EPV-6500-\*-08: 16 mm



**Note:**

These graphs should only be used for representation of flow and pressure through each type of vent and not used for calculating purge time. They can be used for estimating purge time but the actual purge time will be automatically calculated by the 6500 control unit. These graphs are used to determine which vent type will be best suited for the application.

**Type Code**

**E P V - 6 5 0 0 - A A - 0 1**



**Series of vents**  
6500 EPV-6500 vent



**Material**  
AA 6000 series aluminum anodized body and cap  
SS 6000 series aluminum anodized body and 316L stainless steel cap



**Configuration**  
01 High flow rate, low enclosure pressure, high leakage rate  
03 Medium flow rate, medium encl pressure, medium leakage rate  
05 Low flow rate, High enclosure pressure, low leakage rate  
07 Continuous flow, 17 l/min to 85 l/min(0.6 to 3.0 scfm)  
08 Continuous flow, 71 l/min to 226 l/min(2.5 to 8.0 scfm)

Release date: 2023-01-20 Date of issue: 2023-01-20 Filename: t179721\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".