



Thin Client Unit

TCU1200-*

- Modular, lightweight design
- Low-power design with minimal heat dissipation
- VisuNet RM Shell installed
- High connectivity flexibility due to multiple interface options
- Certified for ATEX and IECEx Zone 2/22
- UL listed for USA and Canada
- IP66

Thin Client Unit



Function

The TCU1200-* Thin Client Unit is an ATEX/IECEx certified, UL listed device intended for use in potentially explosive atmospheres, such as Zone 2/22 and Class I/II, Div. 2, and Class III.

Connected to a Pepperl+Fuchs display unit device, it serves as a thin-client based computing unit that runs Pepperl+Fuchs VisuNet RM Shell firmware. The TCU1200 enables users to easily connect to a host system via Ethernet.


Two USB Ex i interfaces support the connection of intrinsically safe accessories that match with the provided entity parameters like Pepperl+Fuchs' EXTA2 keyboard and mouse system.

The USB Ex e interface can be used to connect other third party devices which comply with the installation requirements.

For extended distances, the TCU1200-* is available with an optional multi-mode fiber optic interface.

The TCU1200-* Thin Client unit is used in combination with the modular Pepperl+Fuchs HMI components Display unit (DPU1200-*) and power supply unit (PSU1200-*) of the VisuNet GXP product line.

Dimensions



Technical Data

Hardware

Processor	Intel Bay Trail E3827, 1.75 GHz
RAM	2 GB DDR3L
Mass storage	32 GByte industrial grade MLC SSD

Supply

Input voltage	24 V DC \pm 10 % (SELV/PELV)
Power consumption	14 W average, 30 W max.

Interface

Interface type	<p>Standard:</p> <ul style="list-style-type: none"> 1 x Ethernet 100/1000BASE-TX (Ex e) or 1 x fiber optic 1000BASE-SX (Multimode) or 1 x fiber optic 1000BASE-LX (Singlemode), 1 x USB 2.0 (Ex e), 2 x USB 1.1 (Ex i; intended for Pepperl+Fuchs keyboard and mouse), <p>Optional:</p> <ul style="list-style-type: none"> 1 x barcode reader interface Pepperl+Fuchs Pscan-D/B (Ex i) <p>"S3": 1 x barcode reader interface for wired 1-D scanners IDM-160-D*, IDM-Z1-160-D* and base station IDMx61-B-* and IDM-Z1-x61-B-* (Ex i)</p> <p>"S4": 1 x barcode reader interface for wired 2-D Scanner IDM-Z1-260-D-* (Ex i)</p> <p>"S5": 1 x RS-232 interface with Power Supply for miscellaneous devices and peripherals (Ex i)</p> <ul style="list-style-type: none"> 1 x RS-232 (Ex e) 1 x RS-485 (Ex e) 1 x Ethernet 100/1000Base-TX (Ex e) <p>Bluetooth v4.0, communication distance up to 30 m in open terrain, transmission power +8 dBm, transmission frequency 2.402 ... 2.48 GHz</p>
----------------	---





Release date: 2022-03-23 Date of issue: 2022-03-23 Filename: t183574_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Technical Data

Directive conformity	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations) ; EN 61000-6-4:2007+A1:2011
RoHS	
Directive 2011/65/EU (RoHS)	EN 50581:2012-09
Software	
Operating system	VisuNet RM Shell (based on Windows® 10 IoT LTSB)
Ambient conditions	
Operating temperature	-20 ... 65 °C (-4 ... 149 °F)
Storage temperature	-20 ... 65 °C (-4 ... 149 °F)
Relative humidity	93% at 40°C, non-condensating, according to EN 60068-2-78
Shock resistance	18 shocks 15 g , 11 ms all axis, IEC 60068-2-27
Vibration resistance	10 ... 150 Hz, +/- 0.075 mm , 1g, 10 cycles per axis according to EN60068-2-6
Mechanical specifications	
Degree of protection	IP66 (when mounted on the display unit from Pepperl+Fuchs)
Material	
Housing	anodized aluminum
Mass	approx. 4 kg
Dimensions	280 mm x 240 mm x 43 mm
Data for application in connection with hazardous areas	
EU-type examination certificate	BVS 16 ATEX E 082 X
Marking	Ⓜ II 3G Ex ec [ib] IIC T4 IP66 Gc Ⓜ II 3D Ex tc [ib] IIIC T85°C IP66 Dc
Directive conformity	
Directive 2014/34/EU	EN 60079-0:2012+A11:2013, EN 60079-7:2015, EN 60079-11:2012, EN 60079-31:2014
International approvals	
UL approval	E492874
Approved for	Class I, Division 2, Groups A, B, C, D T4; Zone 2, Group IIC T4 Class II, Division 2, Groups F, G T4; Zone 22, Group IIIB T85 Class III; Zone 22, Group IIIA T85
IECEx approval	IECEx BVS 16.0060X
Approved for	Ex ec [ib] IIC T4 IP66 Gc Ex tc [ib] IIIC T85°C IP66 Dc
Standards	IEC 60079-0:2011, IEC 60079-7:2015, IEC 60079-11:2011, IEC 60079-31:2013

Accessories

	DATL-FO-MM-*	Fiber Optic Multi-Mode Breakout Cable
	1002MC-SX	Gigabit Industrial Media Converter
	DATL-FO-SM-LC-LC-15	Fiber Optic Single-Mode Breakout Cable
	DATL-FO-SM-LC-SC-15	Fiber Optic Single-Mode Breakout Cable

Type Code

TCU1200-* Thin Client Unit Type Code

CPU Unit	Ex Protection	Interfaces	Module A	Module B	Computing Platform	Options & Customization
CPU Unit						
TCU1200	Thin Client Unit (Platform: Zone 2/22; GXP product group, version 0)					
Ex Protection						
J2	IECEX & ATEX II (2) 3 GD; Zone 2/22					
Interfaces						
ET	1x 1000BASE-T LAN Ex e, 1x USB Ex e, 2x USB Ex i					
SX	1x 1000BASE-SX fiber optic (Multimode), 1x USB Ex e, 2x USB Ex i					
LX	1 x 1000BASE-LX fiber optic (Singlemode), 1x USB Ex e, 2x USB Ex i					
Module A						
NN	No additional interface module					
BR	1x TTY Ex i for Barcode Reader (PSCAN-D / EX Dragon) and Base station (PSCAN-B)					
S1	1x RS232 Ex e					
S2	1x RS485 Ex e					
S3	1 x Ex i interface for wired 1-D barcode readers IDM-160-D*, IDM-Z1-160-D-* and base station IDMx61-B-* and IDM-Z1-x61-B-*					
S4	1 x Ex i interface for 2-D barcode readers IDM-Z1-260-D-*					
S5	1 x RS-232 Ex i interface for miscellaneous devices and peripherals					
ET	1x 1000BASE-T LAN Ex e					
Module B						
NN	No additional interface module					
BR	1x TTY Ex i for Barcode Reader (PSCAN-D / EX Dragon) and Base station (PSCAN-B)					
S1	1x RS232 Ex e					
S2	1x RS485 Ex e					
S3	1 x Ex i interface for wired 1-D barcode readers IDM-160-D*, IDM-Z1-160-D-* and base station IDMx61-B-* and IDM-Z1-x61-B-*					
S4	1 x Ex i interface for 2-D barcode readers IDM-Z1-260-D-*					
S5	1 x RS-232 Ex i interface for miscellaneous devices and peripherals					
ET	1x 1000BASE-T LAN Ex e					
Computing Platform						
TS2	Intel® Atom Bay Trail E3827 (1.75 GHz), 2 GB RAM, 32 GB SSD, RM Shell 5.x (based on Windows 10 IoT)					
Options & Customization						
N0	Standard (No customization)					

Example: TCU1200-J2-ET-NN-NN-TS2-N0