



## FB Remote I/O Field Unit

FB9224-T6\*-\*-\*-\*\_\*\_\*-Y\*

- Preconfigured enclosures for engineered FB systems
- Installation in Zone 1 and Zone 21
- Installation in Zone 2 and Zone 22
- Max. 24 slots for I/O modules
- Impact resistance enclosure, IP66
- For PROFIBUS DP, PROFIBUS DP V1, MODBUS RTU and MODBUS TCP
- Image is generic for this device type and may deviate from the specific variant


Field Unit, Stainless Steel



### Function

This field unit is designed to meet the requirements of the most demanding hazardous area and industrial environmental applications. Brushed stainless steel 316L provides high corrosion and impact resistance at a very wide temperature range. It is equipped with a base backplane. It provides 24 slots for I/O modules. The I/O modules can be plugged anywhere on each slot. The fieldbus and power supply are equipped with non-redundant connections.

**Dimensions**



**Technical Data**

<b>General specifications</b>	
Installed components	1x backplane FB9262BP24110.x
<b>Slots</b>	
Bus coupler	1
Bus termination	1
Supply	1
I/O modules (single width)	max. 24
I/O modules (dual width)	max. 12
<b>Supply</b>	
Connection	screw terminals, max. 10 mm <sup>2</sup>
Rated voltage	U <sub>r</sub> 24 V DC/115 V AC/230 V AC , depends on power supply
Redundancy	no
<b>Fieldbus connection</b>	
Fieldbus type	PROFIBUS DP/DP-V1, MODBUS RTU, or MODBUS TCP , depends on bus coupler
Connection	spring terminal, max. 2.5 mm <sup>2</sup>
Redundancy	no
<b>Directive conformity</b>	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61439-1:2012 (J.9.2.2 b) , EN 61439-2:2012
<b>Conformity</b>	
Degree of protection	EN 60529
Impact resistance	EN 60079-0

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t196794\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

**Technical Data**

<b>Ambient conditions</b>	
Ambient temperature	-20 ... 40 °C (-4 ... 104 °F) further on request
Storage temperature	-25 ... 70 °C (-13 ... 158 °F)
Relative humidity	< 75 % (annual mean) < 95 % (30 d/year), no moisture condensation
Shock resistance	shock type I, shock duration 11 ms, shock amplitude 15 g, number of shocks 18
Vibration resistance	frequency range 10 ... 150 Hz; transition frequency: 57.56 Hz, amplitude/acceleration ± 0.075 mm/1 g; 10 cycles frequency range 5 ... 100 Hz; transition frequency: 13.2 Hz amplitude/acceleration ± 1 mm/0.7 g; 90 minutes at each resonance
Impact resistance	7J
<b>Mechanical specifications</b>	
Enclosure cover	hinged door with quarter-turn key locks
Cover seal	foamed silicone
Degree of protection	IP66
<b>Cable entry face B</b>	
M16 quantity	90
M16 series	Cable Glands, Plastic
M16 type	CG.PIDS1.M16.*
M16 clamping range	4 ... 8 mm
M16 info	field signals
M20 quantity	4
M20 series	Cable Glands, Plastic
M20 type	CG.PEDS1.M20.*
M20 clamping range	6 ... 12 mm
M20 info	Fieldbus
M25 quantity	2
M25 series	Cable Glands, Plastic
M25 type	CG.PEDS1.M25.*
M25 clamping range	10 ... 18 mm
M25 info	Power Supply
<b>Terminal assembly</b>	
Number of horizontal rails	1
Usable length per horizontal rail	470 mm
Terminal type	max. 90 spring terminal or screw terminal
<b>Material</b>	
Enclosure	1.5 mm AISI 316L, (1.4404) stainless steel
Finish	brushed
Cable gland	Polyamide (PA)
Seal	housing: foamed silicone cable gland: chloroprene
Mass	approx. 32 kg , without modules
<b>Dimensions</b>	
External dimension (A)	600 mm
External dimension (B)	600 mm
External dimension (C)	260 mm
Mounting	4 Mounting bracket for wall mounting included in the scope of delivery
Grounding	M8 internal/external brass nickel-plated grounding bolt
<b>Data for application in connection with hazardous areas</b>	
EU-type examination certificate	PTB 97 ATEX 1075 X
Marking	Ⓜ II 2(1)G Ex db eb ia mb q [ia Ga/ib] IIC T4 Gb Ⓜ II 2(1)D Ex tb [ia Da/ib] IIIC T130°C Db
Directive conformity	
Directive 2014/34/EU	EN 60079-0:2018 , EN 60079-1:2014 , EN 60079-5:2015 , EN 60079-7:2015 , EN 60079-11:2012 , EN 60079-18:2015 , EN 60079-31:2014
<b>General information</b>	

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t196794\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

Ordering information	This device will be delivered completely configured and assembled ready for use. For configuration details please contact Customer Service.
Supplementary information	EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see <a href="http://www.pepperl-fuchs.com">www.pepperl-fuchs.com</a> .

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t196794\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
[www.pepperl-fuchs.com](http://www.pepperl-fuchs.com)

USA: +1 330 486 0002  
[pa-info@us.pepperl-fuchs.com](mailto:pa-info@us.pepperl-fuchs.com)

Germany: +49 621 776 2222  
[pa-info@de.pepperl-fuchs.com](mailto:pa-info@de.pepperl-fuchs.com)

Singapore: +65 6779 9091  
[pa-info@sg.pepperl-fuchs.com](mailto:pa-info@sg.pepperl-fuchs.com)

