



## Redundancy Field Unit, Stainless Steel

LB9523-T7\*-\*-\*-\*\_\*\_\*\_\*-Y\*

- Preconfigured enclosures for engineered LB systems
- Max. 22 slots for I/O modules
- Installation in Zone 2 or safe area
- Impact resistance enclosure, IP66
- For PROFIBUS DP, PROFIBUS DP V1, PROFINET, and MODBUS RTU
- Redundancy (field bus and power supply)
- Image is generic for this device type and may deviate from the specific variant

### Redundancy Field Unit, Stainless Steel



### Function

This field unit is designed to meet the requirements of the most demanding hazardous area and industrial environmental applications.

Brushed stainless steel 316L provides high corrosion and impact resistance at a very wide temperature range.


It is equipped with a base backplane which allows redundancy in gateway and power supply.

It provides 22 slots for I/O modules.

The I/O modules can be plugged anywhere on each slot.

The fieldbus and power supply are equipped with redundant connections.

**Dimensions**



**Technical Data**

**General specifications**

Installed components backplane LB9022E

**Slots**

Bus coupler 2  
 Supply 3  
 I/O modules (single width) max. 22  
 I/O modules (dual width) max. 11

**Supply**

Connection screw terminals, max. 10 mm<sup>2</sup>  
 Rated voltage U<sub>r</sub> 24 V DC  
 Redundancy yes

**Fieldbus connection**

Fieldbus type PROFIBUS DP/DP-V1, PROFINET or MODBUS RTU , depends on bus coupler  
 Connection 9-pin Sub-D connector (not included with delivery)  
 Redundancy yes

**Directive conformity**

Electromagnetic compatibility  
 Directive 2014/30/EU EN 61439-1:2012 (J.9.2.2 b) , EN 61439-2:2012

**Conformity**

Degree of protection EN 60529  
 Impact resistance EN 60079-0

**Ambient conditions**

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t197126\_eng.pdf

## Technical Data

Ambient temperature	-20 ... 40 °C (-4 ... 104 °F) further on request
Storage temperature	-25 ... 70 °C (-13 ... 158 °F)
Relative humidity	< 75 % (annual mean) < 95 % (30 d/year), no moisture condensation
Shock resistance	shock type I, shock duration 11 ms, shock amplitude 15 g, number of shocks 18
Vibration resistance	frequency range 10 ... 150 Hz; transition frequency: 57.56 Hz, amplitude/acceleration ± 0.075 mm/1 g; 10 cycles frequency range 5 ... 100 Hz; transition frequency: 13.2 Hz amplitude/acceleration ± 1 mm/0.7 g; 90 minutes at each resonance
Impact resistance	7J
<b>Mechanical specifications</b>	
Enclosure cover	hinged door with quarter-turn key locks
Cover seal	foamed silicone
Degree of protection	IP66
Cable entry face B	
M16 quantity	192
M16 series	Cable Glands, Plastic
M16 type	CG.PIDS1.M16.*
M16 clamping range	4 ... 8 mm
M16 info	field signals
M20 quantity	4
M20 series	Cable Glands, Plastic
M20 type	CG.PEDS1.M20.*
M20 clamping range	6 ... 12 mm
M20 info	Fieldbus
M25 quantity	2
M25 series	Cable Glands, Plastic
M25 type	CG.PEDS1.M25.*
M25 clamping range	10 ... 18 mm
M25 info	Power Supply
Terminal assembly	
Number of vertical rails	3
Usable length per horizontal rail	210 mm
Terminal type	max. 120 spring terminal or screw terminal
Material	
Cable gland	Polyamide (PA)
Seal	housing: foamed silicone cable gland: chloroprene
Mass	approx. 25 kg , without modules
Dimensions	
External dimension (A)	800 mm
External dimension (B)	800 mm
External dimension (C)	300 mm
Mounting	4 Mounting bracket for wall mounting included in the scope of delivery
Grounding	M8 internal/external brass nickel-plated grounding bolt
<b>Data for application in connection with hazardous areas</b>	
EU-type examination certificate	
Marking	⊕ II 3(1/2)G Ex eb nA [ia Ga/ib Gb/ic] IIC T4 Gc ⊕ II 3(1/2)D Ex tb [ia Da/ib Db/ic] IIIC T130°C Dc
Certificate	PF 16 CERT 1267 X
Directive conformity	
Directive 2014/34/EU	EN 60079-0:2018 , EN 60079-7:2015 , EN 60079-11:2012 , EN 60079-15:2010 , EN 60079-31:2014
<b>General information</b>	
Ordering information	This device will be delivered completely configured and assembled ready for use. For configuration details please contact Customer Service.

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t197126\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.comUSA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.comGermany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

**PEPPERL+FUCHS**

## Technical Data

Supplementary information

EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see [www.pepperl-fuchs.com](http://www.pepperl-fuchs.com).

Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: t197126\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
[www.pepperl-fuchs.com](http://www.pepperl-fuchs.com)

USA: +1 330 486 0002  
[pa-info@us.pepperl-fuchs.com](mailto:pa-info@us.pepperl-fuchs.com)

Germany: +49 621 776 2222  
[pa-info@de.pepperl-fuchs.com](mailto:pa-info@de.pepperl-fuchs.com)

Singapore: +65 6779 9091  
[pa-info@sg.pepperl-fuchs.com](mailto:pa-info@sg.pepperl-fuchs.com)

 **PEPPERL+FUCHS**