


Safety light curtain SLC30-1800/151



Sensing range up to 15 m

- Resolution 30 mm (hand protection)
- Protective field height up to 1800 mm
- Self-monitoring (type 4 according to IEC/EN 61496-1)
- Master/Slave detection, Plug and Play
- Start/Restart disable
- Degree of protection IP67
- Integrated function display
- Pre-fault indication
- Optional with relay monitor (Option 129)
- Connection via appliance socket M12 x b1
- Safety outputs OSSD in potential-separated semiconductor version

Dimensions



Technical Data

SLC30-1800-T/92		
SLC30-1800-R/151		
General specifications		
0.2 15 m		
IRED		
modulated infrared light		
exempt group		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical Data		
Tests		IEC/EN 61496
Safety type according to IEC/EN 61496		4
Width of protected area		0.2 15 m
Protection field height		1800 mm
Number of beams		96
Operating mode		can be selected with or without start/restart disable
Optical resolution		30 mm
Angle of divergence		<5 °
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 3
Performance level (PL)		PLe
Category		Cat. 4
Mission Time (T _M)		20 a
PFH _d		1.5 E-8
Туре		4
Indicators/operating means		T
Operation indicator		7-segment display in emitter
Diagnostics indicator		7-segment display in receiver
Function indicator		in receiver:
Function indicator		LED red: OSSD off LED green: OSSD on LED yellow: Protected area free, system start-ready
Pre-fault indicator		LED orange
Control elements		switch for start/restart disable, transmission coding
Electrical specifications		
Operating voltage	U _B	24 V DC (-30 %/+25 %)
No-load supply current	Io	Emitter: ≤ 100 mA receiver: ≤ 150 mA
Protection class		11
Input		
Activation current		approx. 10 mA
Activation time		0.03 1 s
Test input		Reset-input for system test (not for option /129)
Function input		Start release
Output		
Safety output		2 separated fail safe semiconductor outputs
Signal output		1 PNP, max. 100 mA for start readiness
Switching voltage		Operating voltage -2 V
Switching current		max. 0.5 A
Response time		30 ms
Conformity		
Functional safety		ISO 13849-1
Product standard		EN 61496-1 ; IEC 61496-2
Approvals and certificates		
CE conformity		CE
UL approval		cULus Listed
CCC approval		CCC approval / marking not required for products rated \leq 36 V
TÜV approval		
Ambient conditions		
Ambient temperature		0 55 °C (32 131 °F)
Storage temperature		-25 70 °C (-13 158 °F)
Relative humidity		max. 95 %, not condensing
Mechanical specifications		max. 55 %, not condensing
Housing length L		1910 mm
Degree of protection		IP67
		II 07

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Safety light curtain

SLC30-1800/151

Technical Data	
Connection	Emitter: M12 connector, 4-pin Receiver: M12 connector, 8-pin
Material	
Housing	extruded aluminum profile, RAL 1021 (yellow) coated
Optical face	Plastic pane
Mass	Per 5700 g

Connection Assignment

Emitter

Receiver

Ready +UB

Restart

OSSD1

OSSD2


0 V

Shield

Test (/129 RM)




Connection Assignment



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

3

Characteristic Curve



Matching system components

SB4-OR-4XP-B-4159	Safety control unit
SB4-OR-4XP	Safety control unit
SB4-OR-4XP-B	SB4 series safety control unit with 1 optional module slot for functional enhancement

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

Release date: 2020-03-23 Date of issue: 2020-10-06 Filename: 199761_eng.pdf

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

EPPERL+FUCHS

SLC30-1800/151

4

Matching system components

SB4-OR-4XP-B-B	SB4 series safety control unit with optional module slots for functional enhancement
SB4-OR-4XP-B-B-B	SB4 series safety control unit with optional module slots for functional enhancement
SB4-OR-4XP-B-B-B-B	SB4 series safety control unit with optional module slots for functional enhancement
SB4-OR-4XP-B-B-B-B-B B	SB4 series safety control unit with optional module slots for functional enhancement
SB4-OR-4XP-B-4158	Safety control unit
SB4-OR-4XP-3819	Safety control unit
SB4-OR-4XP-4M	Safety control unit
SB4-OR-4XP-4MD	Safety control unit
SB4-OR-4XP-4M-4136	Safety control unit of series SB4
SB4-OR-4XP-4X	Safety control unit
SB4-OR-4XP-4X-3819	Safety control unit
SB4-OR-4XP-4136	Safety control unit of series SB4

Accessories

PG SLC-1800	Protective glass panes for SLC series
	roteotive glass parter of OEO series

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

5

Notes

Master slave mode

Master: SLC..-... (semiconductor) or

SLC..-.../31 (relay)

Slave: SLC..-...-S

Using slaves makes it possible to lengthen protective fields or to form protective fields that lie in more than just one level. When you select slaves that can be connected, you should take into consideration that the maximum number of 96 light rays must not be exceeded.

There are slaves for transmitters and receivers. These may simply be connected to the master light curtain. As many as 2 slaves may be connected respectively to the transmitter and receiver unit.

Installation:

- 1. The end cap should be screwed off for the light curtain (without cable gland).
- 2. The plug-in jumper on the connectors of the printed circuit board, which is now visible, should be removed.
- 3. The slave is designed so that the cap located on the cable connector can be plugged directly onto the open end of the light curtain with the printed circuit board.
- 4. After you have screwed on the connection cap, the system is complete.

System accessories

- Mounting set SLC
- Test rods SLC14/SLC30/SLC60
- Protective glass pieces for SLC (to protect the optically functional surface)
- Lateral screwed connection SLC
- Profile alignment aid
- Laser alignment aid SLC
- · Mirror for SLC (for securing hazardous areas on multiple sides)
- Ground pillar UC SLP/SLC
- Housing for pillar
- Enclosure UC SLP/SLC
- Collision protector Damping UC SLP/SLC

Refer to "General Notes Relating to Pepperl+Fuchs Product Information